



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



Operating Temperature (Max): 175 °C

Expanded Inside Diameter (Min): 2.67 mm [.105 in]

Recovered Inside Diameter (Max): .76 mm [.03 in]

Pre-Installed Lead: **Yes**

Resistance Properties: **Immersion Protection**

Features

Product Type Features

Interconnect Device Splice Type	Shield Terminator
Temperature Indicator Type	Thermochromic
Temperature Indicator	Yes

Configuration Features

Pre-Installed Lead Type	Braid Strap
Pre-Installed Lead	Yes

Body Features

Lead Plating Material	Nickel
Lead Stranding	40x38 AWG

Dimensions

Pre-Installed Lead Wire Size	.32 mm ²
Dielectric Outside Diameter (Max)	.75 mm [.03 in]
Shield Outside Diameter (Min)	1.4 mm [.055 in]
Compatible Jacket Diameter Range	2.65 mm [.105 in]
Product Length	16.5 mm [.65 in]
Expanded Inside Diameter (Min)	2.67 mm [.105 in]
Recovered Inside Diameter (Max)	.76 mm [.03 in]

Usage Conditions



Operating Temperature (Max)	175 °C
Resistance Properties	Immersion Protection
Wire Temperature (Max)	150 °C

Industry Standards

MIL/NAS Specification (MIL-S-83519, NAS-1747)	No
Government Qualified	No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #ZPF00000000163673
983-6RS 14-07 SY

TE Part #ZPF00000000200188
699-8081-07

TE Part #EH3336-000
0022E0111-9-G039



TE Part #F35800-000
55PC1113-22-9-9CS3049



TE Part #F13339-000
55PC1116-24-9-9CS3074



TE Part #EK2776-000
55PC2113-22-9-9CS2949



TE Part #CX6545-000
55PC2123-20-6/9-4CS2950

TE Part #696881-1
COPALUM,SLD,R,3/0AL 3/8

TE Part #ZPF00000000202064
741-8256-04



TE Part #CV5203-000
BNX40AC00-2420AX-CS9062

Documents

Product Drawings

[SO96-2-01](#)

English

Datasheets & Catalog Pages

[1654025_Sec8_B-155_CWT_SO63_S01to03_SO96](#)

English

Raychem Electrical Interconnect Products

English