



## Main

Range	ClimaSys
Product name	CU
Product or component type	Cooling unit
Mounting type	Roof of enclosure
Installation	Indoor roof
Product destination	For enclosure
Mounting mode	By screws
Supply Voltage	230 V AC at 50/60 Hz, 1 phase
Rated Power	650 W
Cooling power	650 W 50/60 Hz L35-L35 580 W 50/60 Hz L35-L50

## Complementary

Height	368 mm
Width	400 mm
Depth	325 mm
[In] rated current	2.2 A
Inrush current	6 A
Power consumption in W	340 W at 50/60 Hz, L35-L35 390 W at 50/60 Hz, L35-L50
Energy efficiency ratio	1.9
Control type	Electronic controller
Temperature setting range	20...50 °C at 50/60 Hz
Ambient air temperature for operation	20...50 °C at 50/60 Hz inside the enclosure: 5...55 °C at 50/60 Hz outside the enclosure:
Noise level	55 dB
Pressure	28 bar
Flow rate	Internal circuit: 180 m3/h at 50/60 Hz External circuit: 408 m3/h at 50/60 Hz
Net weight	16.8 kg
Cooling gas type	R134a (0.120 kg)
Type of filter	Optional external circuit filter
Protection type	Circuit breaker protection: miniature circuit breaker (MCB)
Protection type	Thermal protection: T 15 A Short-circuit protection (magnetic):
Material	Steel
Colour	Grey (RAL 7035)

## Environment

Product certifications	UL IEC
Directives	2006/42/EC - machinery 2014/30/EU - electromagnetic compatibility 2011/65/EU - RoHS
Standards	EN/ISO 12100 EN 60335-1 EN 60335-2-40 EN 61000-3-2 EN 61000-3-3 EN 61000-6-2 EN 61000-6-3 EN/IEC 63000:2018 EN 14511
IP degree of protection	IP54 conforming to IEC 60529 (on the internal circuit) IP24 conforming to IEC 60529 (on the external circuit)

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	40 cm
Package 1 Width	45 cm
Package 1 Length	35.5 cm
Package 1 Weight	18.8 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	8
Package 2 Height	94.4 cm
Package 2 Width	120 cm
Package 2 Length	80 cm
Package 2 Weight	175.4 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins