



Main

Range	ClimaSys
Product name	CU
Product or component type	Cooling unit
Mounting type	Roof of enclosure
Installation	Indoor roof
Product destination	For enclosure
Mounting mode	By screws
Supply Voltage	400...460 V AC at 50/60 Hz, 3 phases
Rated Power	4000 W
Cooling power	4000 W 50/60 Hz L35-L35 3300 W 50/60 Hz L35-L50

Complementary

Height	456 mm
Width	795 mm
Depth	575 mm
[In] rated current	4.1 A
Inrush current	28 A
Power consumption in W	1480 W at 50/60 Hz, L35-L35 1770 W at 50/60 Hz, L35-L50
Energy efficiency ratio	2.7
Control type	Electronic controller
Temperature setting range	20...50 °C at 50/60 Hz
Ambient air temperature for operation	20...50 °C at 50/60 Hz inside the enclosure: 5...55 °C at 50/60 Hz outside the enclosure:
Noise level	72 dB
Pressure	32 bar
Flow rate	Internal circuit: 1200 m ³ /h at 50/60 Hz External circuit: 1400 m ³ /h at 50/60 Hz
Net weight	57.2 kg
Cooling gas type	R134a (0.545 kg)
Type of filter	Optional external circuit filter
Protection type	Circuit breaker protection: miniature circuit breaker (MCB)
Protection type	Thermal protection: T 15 A Short-circuit protection (magnetic):
Material	Steel
Colour	Grey (RAL 7035)

Environment

Product certifications	UL IEC
Directives	2006/42/EC - machinery 2014/30/EU - electromagnetic compatibility 2011/65/EU - RoHS
Standards	EN/ISO 12100 EN 60335-1 EN 60335-2-40 EN 61000-3-2 EN 61000-3-3 EN 61000-6-2 EN 61000-6-3 EN/IEC 63000:2018 EN 14511
IP degree of protection	IP54 conforming to IEC 60529 (on the internal circuit) IP24 conforming to IEC 60529 (on the external circuit)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	49 cm
Package 1 Width	83 cm
Package 1 Length	62.5 cm
Package 1 Weight	62.2 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins