


RoHS
Compliant



Device Schematic



Applications

- High Efficiency Switch Mode Power Supplies
- Electronic Lamp Ballasts Based on Half Bridge
- LED Power Supplies

Features

- $R_{DS(ON)} = 0.82\Omega @ V_{GS} = 30V$
- Ultra Low Gate Charge
- Low Reverse Transfer Capacitance
- Fast Switching Capability
- Avalanche Energy Specified
- Improved dv/dt Capability, High Ruggedness

Maximum Ratings @TA = +25°C

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	650	V
Gate-Source Voltage	V_{GS}	± 30	
Avalanche Current (Note 2.)	I_{AR}	12	A
Continuous Drain Current	I_D	12	
Pulsed Drain Current (Note 2.)	I_{DM}	48	
Single Pulsed Avalanche Energy (Note 3.)	E_{AS}	790	mJ
Repetitive Avalanche Energy (Note 2.)	E_{AR}	24	
Peak Diode Recovery dv/dt (Note 4.)	dv/dt	4.5	V/ns
Power Dissipation	P_D	51	W
Junction Temperature	T_j	150	°C
Operating Temperature Range	T_{OPR}	-55 to +150	
Storage Temperature Range	T_{STG}		

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.
 2. Repetitive Rating : Pulse width limited by maximum junction temperature.
 3. $L = 10mH, I_{AS} = 12A, V_{DD} = 50V, R_G = 25\Omega, \text{Starting } T_J = 25^\circ C$
 4. $I_{SD} \leq 12A, di/dt \leq 200A/\mu s, V_{DD} \leq BV_{DSS}, \text{Starting } T_J = 25^\circ C$

N Channel MOSFET

multicomp PRO

Electrical Characteristics @TA = +25°C

Parameter	Test Conditions	Symbol	Min.	Typ.	Max.	Unit
OFF Characteristics						
Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	V_{DSS}	650		--	V
Gate-Source Leakage Current	$V_{DS}=0V, V_{GS}=30V$	I_{GSS}	--	--	100	nA
Gate-Source Leakage Current	$V_{DS}=0V, V_{GS}=-30V$				-100	
Drain-Source Leakage Current	$V_{DS}=650V, V_{GS}=0V$	I_{DSS}	--		1	μA
Breakdown Voltage Temperature Coefficient	$I_D=250\mu A$, Referenced to 25°C	$\Delta BV_{DSS}/\Delta T_J$	--	0.7	--	
ON Characteristics						
Gate-Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	$V_{th(GS)}$	2	--	4	V
Static Drain-Source On-State Resistance	$V_{GS}=10V, I_D=6A$	$R_{DS(ON)}$	--	0.65	0.85	Ω
Dynamic Characteristics						
Input Capacitance	$V_{DS}=25V, V_{GS}=0V, F=1MHz$	C_{ISS}	-	1480	1900	pF
Output Capacitance		C_{OSS}	-	200	270	
Reverse Transfer Capacitance		C_{RSS}	-	25	35	
Switching Characteristics						
Turn-On Delay Time	$V_{DD}=325V, I_D=12A, R_G=25\Omega$, (Note 1,2)	$t_{D(ON)}$	-	30	70	ns
Turn-On Rise Time		t_R		115	240	
Turn-Off Delay Time		$t_{D(OFF)}$		95	200	
Turn-Off Fall Time		t_F		85	180	
Switching Characteristics						
Total Gate Charge	$V_{DS}=520V, I_D=12A, V_{GS}=10V$ (Note 1,2)	Q_G	--	42	54	nC
Gate-Source Charge		Q_{GS}		8.6	--	
Gate-Drain Charge		Q_{GD}		21	--	
Drain-Source Diode Characteristics And Maximum Ratings						
Drain-Source Diode Forward Voltage	$I_S=12A, V_{GS}=0V$	V_{SD}	-	--	1.4	V
Maximum Continuous Drain-Source Diode Forward Current		I_S		--	12	A
Maximum Pulsed Drain-Source Diode Forward Current		I_{SM}		--	48	
Reverse Recovery Time	$V_{GS}=0V, I_S=12A$, $di_F/dt=-100A/\mu s$ (Note 1)	t_{RR}		380	--	ns
Reverse Recovery Charge		Q_{RR}	3.5	--	μC	
Notes: 1. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$. 2. Essentially independent of operating temperature						


Dimensions : Millimetres

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

N Channel MOSFET

Outline Dimensions



Part Number Table

Description	Part Number
N Channel MOSFET, 650V, 12A, TO-220F	HMF12N65S

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.