


ROLINE EV Charging Cable Assembly Type2, 1-Phase, 250VAC (1P+N+E), 32 A, 7.4 kW, 3 m

Product No.	19.08.0003
Manufacturer	ROLINE
Manufacturer No.	19.08.0003
EAN (single piece)	7630049628069



Type2 charging cable for electric and hybrid cars with 7.4 kW, 1-phase, 250 V AC

- Enables easy / fast charging at public charging stations and private wall boxes (wallbox)
- Suitable for charging electric and hybrid vehicles
- Mode 3 / Type 2 car charging cable
- Connections: Type 2 on both sides
- For all electric cars with type 2 connection
- Ergonomically shaped plug and coupler
- Moisture protection (IP65 - connected state, IP54 - unconnected cable with protective caps attached)

- 32A / 1- phase (250 VAC)
- Max. Charging power: 7,4 kW

Technical specifications

Manufacturer	ROLINE
Product group	Power Cables
Product type	Electric car charging cable
Colour	black
Length	3 m
Scope of delivery	E-car charging cable, carrying bag
Charging power	7.4 kW

Current	32 A
Number of phases	1-phase
Supported charging technology	Mode-3
Side 1 Connector Type	IEC 62196-2 Type 2 (VDE-AR-E 2623-2-2)
Side 1 Connector Gender	Male
Side 2 Connector Type	IEC 62196-2 Type 2 (VDE-AR-E 2623-2-2)
Side 2 Connector Gender	Female
Cable LSOH	flame retardant
Protection class (IP Code)	IP65 IP54
Mains connection	IEC 62196-2 Type 2 plug, 1Ph.
Operating temperature min.	-30 °C
Operating temperature max.	50 °C
Height	80 mm
Width	360 mm
Depth	360 mm
Weight	2.1 kg
Height of packaging (single piece)	80 mm
Width of packaging (single piece)	360 mm
Depth of packaging (single piece)	360 mm
Package weight (single piece)	2.25 kg