


# ROLINE EV Charging Cable Assembly Type2, 3-Phase, 480VAC (3P+N+E), 16 A, 11 kW, spiral, 7.5 m

<b>Product No.</b>	19.08.0047
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	19.08.0047
<b>EAN (single piece)</b>	7630049628205



## Type2 charging cable for electric and hybrid cars with 11 kW, 3-phase, 480 V AC

- Enables easy / fast charging at public charging stations and private wall boxes (wallbox)
- Suitable for charging electric and hybrid vehicles
- Mode 3 / Type 2 car charging cable
- Connections: Type 2 on both sides
- For all electric cars with type 2 connection
- Ergonomically shaped plug and coupler
- Moisture protection (IP65 - connected state, IP54 - unconnected cable with protective caps attached)
  
- 16A / 3- phase (480 VAC)
- Max. Charging power: 11 kW

### Technical specifications

Manufacturer	ROLINE
Product group	Power Cables
Product type	Electric car charging cable
Colour	black
Length	7.5 m
Scope of delivery	E-car charging cable, carrying bag
Charging power	11 kW

Current	16 A
Number of phases	3-phase
Supported charging technology	Mode-3
Side 1 Connector Type	IEC 62196-2 Type 2 (VDE-AR-E 2623-2-2)
Side 1 Connector Gender	Male
Side 2 Connector Type	IEC 62196-2 Type 2 (VDE-AR-E 2623-2-2)
Side 2 Connector Gender	Female
Cable LSOH	flame retardant
Protection class (IP Code)	IP65 IP54
Technical particularity	spiral
Mains connection	IEC 62196-2 Type 2 plug, 3Ph.
Operating temperature min.	-30 °C
Operating temperature max.	50 °C
Height	40 mm
Width	390 mm
Depth	390 mm
Height of packaging (single piece)	100 mm
Width of packaging (single piece)	370 mm
Depth of packaging (single piece)	370 mm
Package weight (single piece)	2.5 kg