



Lithium Coin Cell - CR 2320

- Reliable energy for your application
- Standard cells and customized packs
- ESD protection
- UL recognized
- Battery Certification Experts



RoHS compliant



Pb free



REACH compliant



Conflict mineral free


Technical Data Sheet · CR 2320

SPECIFICATIONS


Nominal Voltage	3V
Jauch part number	249998 (1pc blister)
Nominal Capacity	155 mAh
Standard Load	15 KΩ
Standard Current	0.2 mA
Max. Continuous Current	3 mA
Max. Pulse Current	18 mA
Operating Temperature	-20°C to +60°C*
Weight	2.65 gr
Chemistry	Li/MnO ₂
UL1642	MH62838

* In applications where the battery is exposed to temperatures >60°C, please contact Jauch.


DIMENSIONS




DISCHARGE CHARACTERISTICS




TEMPERATURE CHARACTERISTICS



PULSE DISCHARGE CHARACTERISTICS



LOAD VS: CAPACITY



Wide assortment of mounting options, including through hole, surface mount and wire terminals.

Contact Jauch for more information

batterytechnology@jauch.com