multicomp PRO

RoHS Compliant



Specifications

Contact Material
Rating
Electrical Life
Mechanical Life
Insulation Resistance
Dielectric Strength
Contact Resistance
Operating Temperature
Travel
Operation Pressure
Ingress Protection
Torque

: Silver
: 16A 250/125V AC
: 16A 125 & 250V AC 50,000 Cycles
: Momentary 1,000,000
: 100MΩ min at 500V DC
: 1,500Vrms@Sea Level
: 50mΩ max.@1A 12V DC (initial value)
: -25°C to 85°C
: About 3.2mm
: 3.5 ±1.5N
: IP67, IK08 (Stainless Steel)
: 1~3Nm


Materials

Bushing	: Stainless Steel
Base	: PBT(UL 94-V0); PC(UL94-V2); PA6T(UL94-V0)
Actuator	: PC(UL 94-V2); Stainless Steel
Inner Assembly	: POM/PA66
Spring	: Steel
Sealing	: Silicone
O-ring	: Silicone
Terminal/Contact	: Brass, Silver plated
Hex Nut	: Nickel plated brass

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Diagram



Part Number Table

	Description	Part Number
Dimensions : Inches (Millimetres)	Anti Vandal Pushbutton Switch, Blue LED, 19mm, 16A	MPW19-A0F0E724-A1ZB

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

