


Unshielded RJ45 Passthrough Connector for CAT6A Cable, Pack of 100 RJ456AUS-100



The Jonard Tools CAT6A RJ45 Pass-Through Connectors are used by network installers/technicians in order to terminate CAT6e, CAT6A, and CAT7A network cables with a pass-through crimper. They are used in households and businesses and are ideal for terminating a round network cable or even replacing an existing connector. These connectors feature the following:

- 50 μ m gold plating on contact surfaces provides greater signal quality than the competition
- Tripoint-type prongs allow you to use stranded or solid CAT6e, CAT6A, and CAT7 cables

- Simplify twisted pair network cable termination by allowing the wires to pass through the connector
- Advantage of the pass-through feature is that you do not have to measure and cut the wires before termination, which can lead to having poor connection and signal loss
- Clear housing allows the operator to see the wire pairs easily
- Wire slots are enlarged for wires up to 1.3 mm in diameter

Specifications

Number of Connectors	100
Cable Type	CAT6e, CAT6A and CAT7
Cable Diameter	26 - 18 AWG (0.4 - 1.3 mm)
Connector Type	Three-prong RJ45
Plating Thickness	50 micro-inches
Standards	ANSI/TIA-568-C.2, UL 1863, FCC Part 68 subpart F
Operating Temperature	-10°C to 60°C
Weight	0 lb (0 g)
UPC #	810053352809