



Field potential distributor module; 18 channels; GND

**Part no.**                    **XN-322-18PD-M**  
**178769**

<b>General specifications</b>		
Product name		Eaton XN-322 Power distributor
Part no.		XN-322-18PD-M
EAN		7640130098336
Product Length/Depth		104.2 millimetre
Product height		16.8 millimetre
Product width		80.3 millimetre
Product weight		0.055 kilogram
Certifications		IEC/EN 61000-6-2 UL File No.: E247993 UL508 IEC/EN 61000-6-4 CE IEC/EN 61131-2
Product Tradename		XN-322
Product Type		Power distributor
Product Sub Type		None
Catalog Notes		Power distribution with XN-322 slice module in XN300 I/O system, 18 channels, GND. Power Distribution, 18 channels, GND
<b>Features &amp; Functions</b>		
Electric connection type		Plug-in connection
Features		Fieldbus connection over separate bus coupler possible
<b>General information</b>		
Degree of protection		IP20
Mounting method		Rail mounting possible
Overvoltage category		III
Pollution degree		3
Product category		XN-322 power supply module
Type		XN300 power supply module
Used with		XN300 XN-312-...
Voltage type		DC
<b>Ambient conditions, mechanical</b>		
Height of fall (IEC/EN 60068-2-32) - max		1 m
Mounting position		Horizontal
Shock resistance		15 g, Mechanical, Half-sinusoidal shock 11 ms, 18 Impacts
Vibration resistance		5 - 8.4 / 8.4 -150 Hz, 3,5 mm / 1 g
<b>Climatic environmental conditions</b>		
Air pressure		795 - 1080 hPa (operation)
Ambient operating temperature - min		0 °C
Ambient operating temperature - max		60 °C
Ambient storage temperature - min		-20 °C
Ambient storage temperature - max		85 °C
Climatic proofing		Damp heat, constant, to IEC 60068-2-3 Dry heat to IEC 60068-2-2
Environmental conditions		Condensation: prevent with appropriate measures
Relative humidity		0 - 95 % (non-condensing)
<b>Electro magnetic compatibility</b>		
Air discharge		4 kV (Contact discharge) 8 kV (Air discharge)
Burst impulse		2 kV, Supply cable

		1 kV, Signal cable
Electromagnetic fields		10 V/m at 0.08 - 1.0 GHz (according to IEC EN 61000-4-3) 1 V/m at 2 - 2.7 GHz (according to IEC EN 61000-4-3) 3 V/m at 1.4 - 2 GHz (according to IEC EN 61000-4-3)
Emitted interference		47 dB (at 230 - 1000 MHz, Class A, radiated, high frequency) 40 dB (at 30 - 230 MHz, Class A, radiated, high frequency)
Radiated RFI		10 V
Surge rating		0.5/0.5 kV, Supply cable, balanced/unbalanced, EMC 1 kV, Signal cable, unbalanced, EMC
Voltage dips		Voltage dips: 10 ms/Voltage fluctuations: Yes
<b>Terminal capacities</b>		
Terminal capacity		24 - 16 AWG 0.25 - 1.5 mm <sup>2</sup> , with ferrules with plastic collar according to DIN 46228-1 (ferrules crimped gas-tight) 0.2 - 1.5 mm <sup>2</sup> , flexible without ferrule, H07V-K 0.2 - 1.5 mm <sup>2</sup> , solid, H07V-U 0.25 - 1.5 mm <sup>2</sup> , with ferrules without plastic collar according to DIN 46228-1 (ferrules crimped gas-tight)
Gauge pin		A1 (according to IEC/EN 60947-1)
Stripping length (main cable)		10 mm
Insulating material group		I
<b>Electrical rating</b>		
Rated operational current (I <sub>e</sub> ) - max		8 A
Rated operational voltage		160 V (terminations)
Supply voltage at AC, 50 Hz - min		0 V AC
Supply voltage at AC, 50 Hz - max		0 V AC
Supply voltage at DC - min		18 V DC
Supply voltage at DC - max		30 V DC
<b>Communication</b>		
Connection type		Push-in spring-cage terminal (plug-in connection), Connection design in TOP direction
<b>Input/Output</b>		
Load current		Not specified by plug manufacturer
<b>Safety</b>		
Explosion safety category for dust		None
Explosion safety category for gas		None
<b>Design verification</b>		
Equipment heat dissipation, current-dependent P <sub>vid</sub>		0 W
Heat dissipation capacity P <sub>diss</sub>		0 W
Heat dissipation per pole, current-dependent P <sub>vid</sub>		0 W
Rated operational current for specified heat dissipation (I <sub>n</sub> )		0 A
Static heat dissipation, non-current-dependent P <sub>vs</sub>		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Meets the product standard's requirements.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.

10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 9.0

Programmable logic controllers PLC (EG000024) / Fieldbus, decentr. periphery - power supply/segment module (EC001600)		
Electric engineering, automation, process control engineering / Control, Process Control System (PCS) / Field bus, decentralized peripheral / Field bus, decentralized peripheral - feed and segment module (ec1@ss13-27-24-26-10 [BAA071018])		
Supply voltage AC 50 Hz	V	0 - 0
Supply voltage AC 60 Hz	V	0 - 0
Supply voltage DC	V	18 - 30
Voltage type (supply voltage)		DC
Number of HW-interfaces industrial Ethernet		0
Number of interfaces PROFINET		0
Number of HW-interfaces RS-232		0
Number of HW-interfaces RS-422		0
Number of HW-interfaces RS-485		0
Number of HW-interfaces serial TTY		0
Number of HW-interfaces parallel		0
Number of HW-interfaces wireless		0
Number of HW-interfaces USB		0
Number of HW-interfaces other		1
With optical interface		No
Supporting protocol for EtherCAT		No
Supporting protocol for TCP/IP		No
Supporting protocol for PROFIBUS		No
Supporting protocol for CAN		No
Supporting protocol for INTERBUS		No
Supporting protocol for ASI		No
Supporting protocol for KNX		No
Supporting protocol for Modbus		No
Supporting protocol for Data-Highway		No
Supporting protocol for DeviceNet		No
Supporting protocol for SUCONET		No
Supporting protocol for LON		No
Supporting protocol for PROFINET IO		No
Supporting protocol for PROFINET CBA		No
Supporting protocol for SERCOS		No
Supporting protocol for Foundation Fieldbus		No
Supporting protocol for EtherNet/IP		No
Supporting protocol for AS-Interface Safety at Work		No
Supporting protocol for DeviceNet Safety		No
Supporting protocol for INTERBUS-Safety		No
Supporting protocol for PROFIsafe		No
Supporting protocol for SafetyBUS p		No
Supporting protocol for other bus systems		No
Radio standard Bluetooth		No
Radio standard WLAN 802.11		No
Radio standard GPRS		No
Radio standard GSM		No
Radio standard UMTS		No
System accessory		Yes
Degree of protection (IP)		IP20

Type of electric connection			Plug-in connection
With potential separation			No
With power supply module			No
Suitable as segment module			No
Remote module			No
Fieldbus connection over separate bus coupler possible			Yes
Bus diagnosis possible			No
Rail mounting possible			Yes
Wall mounting/direct mounting			No
Front built-in possible			No
Rack-assembly possible			No
Suitable for safety functions			No
SIL according to IEC 61508			None
Performance level according to EN ISO 13849-1			None
Appendant operation agent (Ex ia)			No
Appendant operation agent (Ex ib)			No
Explosion safety category for gas			None
Explosion safety category for dust			None
Certified for UL hazardous location class I			No
Certified for UL hazardous location class II			No
Certified for UL hazardous location class III			No
Certified for UL hazardous location division 1			No
Certified for UL hazardous location division 2			No
Certified for UL hazardous location group A (acetylene)			No
Certified for UL hazardous location group B (hydrogen)			No
Certified for UL hazardous location group C (ethylene)			No
Certified for UL hazardous location group D (propane)			No
Certified for UL hazardous location group E (metal dusts)			No
Certified for UL hazardous location group F (carbonaceous dusts)			No
Certified for UL hazardous location group G (non-conductive dusts)			No
Width		mm	80.3
Height		mm	16.8
Depth		mm	104.2