



Variable frequency drive, 230 V AC, 1-phase, 11 A, 2.2 kW, IP20/NEMA0, Radio interference suppression filter, 7-digital display assembly, Setpoint potentiometer, Brake chopper, FS2



Part no. DM1-12011EB-S20S-EM
3-5047-004A
EL Number 4132225
(Norway)

General specifications	
Product name	Eaton DM1 Variable frequency drive
Part no.	DM1-12011EB-S20S-EM
EAN	4015081980680
Product Length/Depth	180 millimetre
Product height	220 millimetre
Product width	109 millimetre
Product weight	2.6 kilogram
Certifications	UkrSEPRO CSA-C22.2 No. 274-17 UL 508C IEC/EN61800-3 CE marking EAC IEC/EN 61800-3 IEC/EN 61800-2 UL Listed IEC/EN 61800-5-1 IEC/EN61800-5 UL File No.: E134360 UL Category Control No.: NMMS, NMMS7 UL report applies to both US and Canada RoHS, ISO 9001 C-Tick CSA-C22.2 No. 274-13 Certified by UL for use in Canada CE CUL UL
Product Tradename	DM1
Product Type	Variable frequency drive
Product Sub Type	None
Catalog Notes	Assigned motor rating: for normal internally and externally ventilated 4 pole, three-phase asynchronous motors with 1500 rpm at 50 Hz or 1800 min at 60 Hz Assigned motor rating: Overload cycle for 60 s every 600 s for PM motors Operation with 110 % overload (1 min./10 min.): -10 to +40 (max. +55 with 1% derating per Kelvin above limit) Operation with 150% overload (1 min./10 min.): -10 to +50 (max. +60 with 1% derating per Kelvin above limit) Rated operational current for a switching frequency of 1 - 16 kHz and an ambient temperature of +50 °C for a 150% overload and +40 °C for a 110% overload
General information	
Air volume capacity	42 m ³ /h
Cable length	C2 ≤ 5 m, maximum motor cable length C3 ≤ 25 m, maximum motor cable length
Communication interface	BACnet MS/TP, built in CANopen®, optional Ethernet IP, built in DeviceNet, optional Modbus RTU, built in Modbus TCP, built in SmartWire-DT, optional BACnet TCP PROFIBUS, optional
Connection to SmartWire-DT	Yes In conjunction with DXG-NET-SWD SmartWire DT module
Degree of protection	IP20 NEMA 0other
Electromagnetic compatibility	1st and 2nd environments (according to EN 61800-3)
Environmental class	3C2, 3S2 (Air quality)
Features	Parameterization: Keypad Parameterization: Power Xpert inControl Temperature-controlled fan

		Parameterization: Fieldbus
Fitted with:		Radio interference suppression filter 7-digital display assembly IGBT inverter Internal DC link Brake chopper Setpoint potentiometer Breaking resistance Control unit PC connection
Frame size		FS2
Mounting position		Vertical
Number of slots		1 (expansion)
Overvoltage category		III
Pollution degree		2
Product Category		Variable frequency drives
Protection		Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
Radio interference class		Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. C1: with external filter, for conducted emissions only
Safety function/level		STO (Safe Torque Off, SIL2, PLc Cat 2)
Shock resistance		0.75 mm (peak) at 10 - 57 Hz, max. 1 g at 57 - 150 Hz, according to EN 61800-5-1, EN 60068-2-6: 10 - 150 Hz
Suitable for		Branch circuits, (UL/CSA)
Climatic environmental conditions		
Altitude		Max. 3000 m Max. 2000 m for Corner Grounded TN Systems Above 1000 m with 1 % derating per 100 m Max. 1000 m
Ambient operating temperature - min		-10 °C
Ambient operating temperature - max		50 °C
Ambient storage temperature - min		-40 °C
Ambient storage temperature - max		70 °C
Climatic proofing		< 95 average relative humidity (RH), no condensation, no corrosion
Main circuit		
Current limitation		0.1 - 2 x I _H (CT), motor, main circuit
Heat dissipation at current/speed		122.2 W at 100% current and 0% speed 161.8 W at 50% current and 0% speed 197.7 W at 100% current and 90% speed 46.4 W at 25% current and 50% speed 56 W at 25% current and 0% speed 70.2 W at 100% current and 50% speed 85.8 W at 50% current and 50% speed 92.8 W at 50% current and 90% speed
Input current ILN at 110% overload		20.1 A
Input current ILN at 150% overload		12.7 A
Mains current distortion		40 %
Mains switch-on frequency		Maximum of one time every 60 seconds
Mains voltage - min		200 V
Mains voltage - max		240 V
Operating mode		Sensorless vector control (SLV) Torque regulation PM motors U/f control Speed control with slip compensation
Output frequency - min		0 Hz
Output frequency - max		400 Hz
Output voltage (U ₂)		230 V AC, single-phase 240 V AC, single-phase 230 V AC, 3-phase 240 V AC, 3-phase
Overload current IL at 110% overload		19.25 A
Overload current IL at 150% overload		16.5 A
Rated conditional short-circuit current (I _q)		100 kA
Rated control supply voltage		10 V DC (U _s , max. 10 mA)

Rated frequency - min		45 Hz
Rated frequency - max		66 Hz
Rated operational current (Ie) at 110% overload		17.5 A
Rated operational current (Ie) at 150% overload		11 A
Rated operational power at 220/230 V, 50 Hz, 1-phase		2.2 kW
Rated operational power at 220/230 V, 50 Hz, 3-phase, 110% overload		4 kW
Rated operational voltage		230 V AC, 1-phase 240 V AC, 1-phase
Resolution		0.01 Hz (Frequency resolution, setpoint value)
Short-circuit protection rating		25 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
Starting current - max		200 %, IH, max. starting current (High Overload), For 2 seconds every 20 seconds, Power section
Supply frequency		50/60 Hz
Switching frequency		4 kHz, 1 - 16 kHz adjustable, fPWM, Power section, Main circuit
System configuration type		TN-S, TN-C, TN-C-S, TT, IT
Voltage rating - max		240 V AC
Motor rating		
Assigned motor current IM at 220 - 240 V, 60 Hz, 150% overload		9.6 A
Assigned motor current IM at 230 V, 50 Hz, 110% overload		14.8 A
Assigned motor current IM at 230 V, 50 Hz, 150% overload		8.7 A
Assigned motor current IM at 230 V, 60 Hz, 110% overload		15.2 A
Assigned motor power at 230/240 V, 60 Hz, 1-phase		3 HP
Assigned motor power at 230/240 V, 60 Hz, 3-phase, 110 % overload		5 HP
Braking function		
Braking resistance		16 Ω
Braking torque		Max. 30 % MN, Standard - Main circuit Max. 100 % of rated operational current Ie with external braking resistor - Main circuit Adjustable to 150 %, DC - Main circuit
Control circuit		
Number of inputs (analog)		1
Number of inputs (digital)		4
Number of outputs (analog)		1
Number of relay outputs		2 (parameterizable, 1 changeover contact and 1 N/O, 3 A (240 V AC) / 3 A (24 V DC))
Rated control voltage (Uc)		24 V DC (external, max. 100 mA options incl.)
Design verification		
Equipment heat dissipation, current-dependent Pvid		201 W
Rated operational current for specified heat dissipation (In)		17.5 A
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.

10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Frequency converter <= 1 kV (EC001857)		
Electric engineering, automation, process control engineering / Electrical drive / Static frequency converter / Static frequency / Servo converter = < 1 kV (ecI@ss13-27-02-31-01 [AKE177019])		
Mains voltage	V	200 - 240
Mains frequency		50/60 Hz
Number of phases input		1
Number of phases output		3
Max. output frequency	Hz	400
Max. output voltage	V	240
Nominal output current I2N	A	11
Max. output at quadratic load at rated output voltage	kW	4
Max. output at linear load at rated output voltage	kW	2.2
Power consumption	W	201
Relative symmetric net frequency tolerance	%	10
Relative symmetric net voltage tolerance	%	10
Number of analogue outputs		1
Number of analogue inputs		1
Number of digital outputs		0
Number of digital inputs		4
With control element		Yes
Application in industrial area permitted		Yes
Application in domestic- and commercial area permitted		Yes
Supporting protocol for TCP/IP		Yes
Supporting protocol for PROFIBUS		Yes
Supporting protocol for CAN		Yes
Supporting protocol for INTERBUS		No
Supporting protocol for ASI		No
Supporting protocol for KNX		No
Supporting protocol for Modbus		Yes
Supporting protocol for Data-Highway		No
Supporting protocol for DeviceNet		No
Supporting protocol for SUCONET		No
Supporting protocol for LON		No
Supporting protocol for PROFINET IO		No
Supporting protocol for PROFINET CBA		No
Supporting protocol for SERCOS		No
Supporting protocol for Foundation Fieldbus		No
Supporting protocol for EtherNet/IP		Yes
Supporting protocol for AS-Interface Safety at Work		No
Supporting protocol for DeviceNet Safety		No
Supporting protocol for INTERBUS-Safety		No
Supporting protocol for PROFIsafe		No
Supporting protocol for SafetyBUS p		No
Supporting protocol for BACnet		Yes
Supporting protocol for other bus systems		Yes
Number of HW-interfaces industrial Ethernet		1
Number of interfaces PROFINET		0
Number of HW-interfaces RS-232		0

Number of HW-interfaces RS-422			0
Number of HW-interfaces RS-485			1
Number of HW-interfaces serial TTY			0
Number of HW-interfaces USB			0
Number of HW-interfaces parallel			0
Number of HW-interfaces other			1
With optical interface			No
With PC connection			Yes
Integrated breaking resistance			Yes
4-quadrant operation possible			Yes
Type of converter			U converter
Degree of protection (IP)			IP20
Degree of protection (NEMA)			Other
Height		mm	220
Width		mm	109
Depth		mm	180