



**Part Number :** [1552410026](#)


**Product Description :** Flamar Sensor Cable, WSOR Jacket, Braided Shielding Overall, 5 Circuits, 0.34mm<sup>2</sup> / 22 AWG, 6.10mm (.240") Diameter, 300.0m (984.25') Length, Black

**Series Number :** 155221

**Status :** Active

**Product Category :** Industrial Cable

**Engineering Number :** BS1-5-3X100M



---

## Documents & Resources

### Specifications

[Product Specification 1552200001-P1E.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Industrial Cable
Series	155221
Description	Flamar Sensor Cable, WSOR Jacket, Braided Shielding Overall, 5 Circuits, 0.34mm <sup>2</sup> / 22 AWG, 6.10mm (.240") Diameter, 300.0m (984.25') Length, Black
Comments	3 reels of 100.0m each
Geographic Area	Global
Product Family	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar,Signal and Control
UPC	889056464079

### Agency

UL	E172949
----	---------

### Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

### Physical

Bending Radius - Minimum	> 7.5xOD
Cable Length	300.0m
Circuits (Loaded)	5
Color - Cable Jacket	Black
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.055/kg
Outer Jacket Diameter	6.10mm
Packaging Type	Reel
Temperature Range - Operating	-25° to +80°C

Wire/Cable Type	UL AWM 21215 / CSA
Wire Size (AWG)	22
Wire Size mm <sup>2</sup>	0.34

---

**Use with Part(s)**

Description	Part Number
Micro-Change (M12) Field Attachable Connectors	<u>120071</u>
Ultra-Lock (M12) Single Keyway Field Attachable Connectors	<u>120085</u>
Nano-Change (M8) Field Attachable Connectors	<u>120091</u>

---