



**Part Number :** [1554215002](#)

**Product Description :** Flamar PROFINET C Network Cable, WSOR Jacket, Braided Shielding Overall, 4 Circuits, 2x(2x0.34mm<sup>2</sup>) / 2x(2x22 AWG), 6.80mm (.268") Diameter, 500.0m (1640.42') Length, Green

**Series Number :** 155421

**Status :** Active

**Product Category :** Industrial Cable

**Engineering Number :** CAB-12-1X500M



---

## Documents & Resources

### Specifications

[Test Summary 1202098313-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead monoxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Industrial Cable
Series	155421
Description	Flamar PROFINET C Network Cable, WSOR Jacket, Braided Shielding Overall, 4 Circuits, 2x(2x0.34mm <sup>2</sup> ) / 2x(2x22 AWG), 6.80mm (.268") Diameter, 500.0m (1640.42') Length, Green
Geographic Area	Global
Product Family	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar,Network
Protocol	PROFINET
UPC	889056464765

### Agency

UL	E172949
----	---------

### Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

### Physical

Bending Radius - Minimum	> 15xOD
Cable Length	500.0m
Circuits (Loaded)	4
Color - Cable Jacket	Green
Insulation	PE
Material - Outer Jacket	WSOR
Net Weight	0.070/kg
Outer Jacket Diameter	6.80mm
Packaging Type	Reel

Temperature Range - Operating	-10° to +60°C
Wire/Cable Type	UL AWM 21215 / CSA
Wire Size (AWG)	22
Wire Size mm <sup>2</sup>	0.34

---

**Use with Part(s)**

Description	Part Number
Micro-Change (M12) Field Attachable Connectors	<u>120071</u>
Micro-Change (M12) Field Attachable Connectors and D-Sub Connectors	<u>120100</u>
Micro-Change (M12) and Mini-Change Trunk and Drop Connectors	<u>130034</u>
Field Attachable Connectors	<u>130047</u>

---