

PHE840MB6220KB12R17

Aliases (F840BM224K275A)

Not for New Design • Recommended Replacement Series R46 X2 310 VAC

PHE840M/F840, Film, Metallized Polypropylene, Safety, 0.22 uF, 10%, 275 VAC (X2), 760 VDC, 105°C, 15mm



Click [here](#) for the 3D model.

Dimensions	
L	18mm MAX
H	15mm MAX
T	8mm MAX
S	15mm +/-0.4mm
LL	17mm NOM
F	0.8mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	400

General Information	
Series	PHE840M/F840
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB Performance	No
Typical Component Weight	2.898 g
Notes	Not for new design – the replacement series is: R46 X2 310VAC.

Specifications	
Capacitance	0.22 uF
Capacitance Tolerance	10%
Voltage AC	275 VAC (X2)
Voltage DC	760 VDC
Temperature Range	-55/+105°C
Rated Temperature	105°C
Dissipation Factor	0.1% 1kHz, 0.4% 10kHz
Insulation Resistance	30 GOhms
Max dV/dt	100 V/us