

PHE844RD6470KR06L2

Aliases (F844DY474K440C, PHE844RD6470KD19R06L2)

PHE844/F844, Film, Metallized Polypropylene, Safety, 0.47 uF, 10%, 440 VAC (X1) (ENEC), 480 VAC (UL, cUL), 1000 VDC, 105°C, 22.5mm



Click [here](#) for the 3D model.

Dimensions	
L	26mm MAX
H	24.5mm MAX
T	15.5mm MAX
S	22.5mm +/-0.4mm
LL	6mm -1mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	176

General Information	
Series	PHE844/F844
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Wire Leads
Safety Class	X1
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB Performance	Yes
Typical Component Weight	10.4 g
Miscellaneous	ClimCat: 40/105/56/B.

Specifications	
Capacitance	0.47 uF
Capacitance Tolerance	10%
Voltage AC	440 VAC (X1) (ENEC), 480 VAC (UL, cUL)
Voltage DC	1000 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Dissipation Factor	0.1% 1kHz, 0.4% 10kHz
Insulation Resistance	21.2766 GOhms
Max dV/dt	100 V/us