



Click [here](#) for the 3D model.

Dimensions

Chip Size	0201
L	0.6mm +/-0.03mm
W	0.3mm +/-0.03mm
T	0.3mm +/-0.03mm
LL	0.15mm +/-0.05mm
B	0.15mm +/-0.05mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	15000

General Information

Series	L-RMS
Style	SMD Chip
Description	Surface Mount Inductor
RoHS	Yes
Core	Ceramic
Winding Type	Multilayer

Specifications

Inductance	0.01 uH
Inductance Tolerance	5%
Temperature Range	-55/+125°C
Current	150 mAmps (MAX)
DC Resistance	0.63 Ohms
Quality Factor	7 at 100 MHz, 14 at 500 MHz, 17 at 800 MHz, 18 at 1000 MHz
Self-Resonant Frequency	2900 MHz