


This document is the property of Amphenol Corporation and is loaned to the customer for use in the design and manufacture of products. It is not to be used for any other purpose, and its use is limited to the specific application and product for which it was intended. Amphenol Corporation and its subsidiaries are not responsible for any errors or omissions in this document or for any consequences arising from its use. All rights are reserved. For more information, see the document.




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A		07/11/07	

D-SUB TECHNICAL DATA

SHELL : Steel, 2.5um (100u") min tin over 1.25um (50u") min nickel
 BODY : Glass filled thermoplastic.
 Flame retardant to UL94 V-0
 CONTACTS : brass.
 0.76um(30u") min gold over 0.65um(25u") min nickel
 ELECTRICAL : Voltage rating :1000 V RMS at 50 Hz
 Current rating 5A.
 Insulation resistance >1000 M Ohms
 Contact resistance 20 mOhms max.
 CLIMATIC : Temperature range -55 °C up to 125°C
 MARKING : Amphenol...(Series No.)
 Commercial reference
 Manufacturing date

PRODUCT CODE

L 717 SD D 50 P C309



UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE	
U.S.	METRIC	DRAWN	Iss. by	7/7/07	7/7/07
T: +/-	0.50	CHECKED	146.4000	7/7/07	7/7/07
XX: +/-	0.30				
ANGLES +/-	0.20				
FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES					
DIMENSIONS U.S. INCHES					
DRAWING FILE :					
ANGLE OF PROJECTION					
TITLE					
Stamped and Formed connector, SD series					
SIZE DRAWING NO.		SCALE		SHEET 1 OF 1	
A4		NONE		A	
C L717SDD50PC309					

Amphenol