



This document is the property of Amphenol Corporation and is returned in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose its use or information in this document.



RECOMMENDED P.C.B LAYOUT
TOLERANCE: +/ -0.05mm

P.C.B EDGE



Customer drawing


REVISIONS			DATE	APPROVED
S/N	ECN	DESCRIPTION		
1	HK--	First Release Drawing	20/Aug/13	JP

D-SUB TECHNICAL DATA

SHELL : SPCC, 100u" min tin over 50u" min nickel over 50u" copper
 BODY : PBT, UL 94V-0, Color:Black.
 CONTACTS : Copper Alloy
 Gold flash plated over 50u" nickel on mating area
 100u" tin plated over 50u" nickel on solder area
 BRACKET : Zinc Alloy, Nickel plated
 BOARDLOCK: Copper Alloy, Tin plated
 ELECTRICAL : Voltage rating 250V AC(RMS)
 Current rating 3A
 Withstanding Voltage >1000 V AC(RMS)
 Insulation resistance >1000 M Ohms
 Contact resistance 25 mOhms max.

PRODUCT CODE

L17H3DD0130



UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE	
TOLERANCES	U.S.	DRAWN	DATE	CHKD	DATE
X +/-	METRIC				
XX +/-					
XXX +/-					
FRACTIONS +/-					
ANGLES +/-					
SEE REMOVED SHARP EDGES					
FOR MATERIALS AND FINISHES					
DIMENSIONS					
ANGLES					
FINISHES					
DRAWING FILE :					
ANGLE OF PROJECTION					
TITLE					
Amphenol					
Amphenol East Asia Limited					
Dual ports D-SUB L17H Series					
SIZE DRAWING NO.					
A4					
SCALE					
NONE					
SHEET 1 OF 1					
REV.					
1					