KERN

IoT-Line Industrial Platform Scale KERN IFC











# The new IFC: Robust industrial scales with up to three interfaces, also with optional verification

### **Features**

- Tough industry standard suitable for use in harsh industrial applications
- Standardised, convenient KERN concept of operation, consistency across products in terms of design, menu structure, button functions, interface connection and interface protocol
- Industry 4.0: Data and control commands can be exchanged through the KERN Universal Port using one interface, which can be connected to the housing, or through three parallel interfaces using the KUP Extension box. The following interfaces are available as an option: RS-232, USB, Ethernet, WiFi, Bluetooth
- Each interface can be set up separately, e.g.:
- Interface 1 (WiFi): Continuous sending to a PC for documentation of a process
- Interface 2 (RS 232): Print stable weight
- Interface 3 (analogue module): Controlling a device when the target weight is reached
- For further information on KUP and KCP see page 20/21
- Available as an option with alibi memory for paperless archiving of weighing results. This also means the results of weighings with mandatory verification can be electronically evaluated and processed further
- Data query and remote control of the balance using a computer or CRM/ERP systems using the KERN Communication Protocol

- Simplified battery replacement through easilyaccessible housing. Particularly advantageous for models with optional verification, as the verification seal remains intact
- In Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65
- Benchtop stand incl. wall mount for display device as standard
- Protective working cover included with delivery
- With Real Time Clock as standard: Enables you
  to log the weighing results with accurate time
  information. Even if the power supply is interrupted, the balance can continue to work with the
  correct time

# <u>KERN</u>

#### IoT-Line Industrial Platform Scale KERN IFC







#### **Technical Data**

- · Large backlit LCD display, digit height 50 mm
- · Weighing plate dimensions, stainless steel
  - **A** W×D×H 400×300×114 mm
  - B W×D×H 500×400×124 mm
  - W×D×H 650×500×136 mm
  - **D** W×D×H 800×600×189 mm
- Dimensions of display device W×D×H 220×145×65 mm
- Cable length of display device approx. 3 m
- Permissible ambient temperature -10 °C/40 °C

#### Accessories

- Protective working cover, scope of delivery 5 items, KERN YBA-A18S05
- Internal rechargeable battery pack, operating time up to 48 h without backlight, charging time approx. 8 h, KERN YKR-01
- Stand to elevate display device, height of stand approx. 1040 mm, KERN BFS-A07
- Column to screw on to the platform, for models with weighing plate size
- A, B, C Height of stand approx. 330 mm, KERN IFB-A01
- **B**, **C** Height of stand approx. 600 mm, KERN IFB-A02
- External data interface RS-232, interface cable included, KERN KUP-01
- External data interface USB, interface cable included, KERN KUP-03
- External data interface Ethernet, KFRN KUP-04
- External data interface WiFi, interface cable included, KERN KUP-05

- Bluetooth interface adapter, KERN KUP-06
- · Analogue module, KERN KUP-08
- S Extension box for connecting up to three interfaces in parallel, KERN KUP-13
- Memory module (alibi memory), KERN YMM-04
- ESD drain to protect against electrostatic discharge e.g. for electrostatically-charged weighing objects or people who work with the scale, KERN YGR-01
- Signal lamp for visual support of weighing with tolerance range, connection is only possible in combination with KUP-01 (RS 232 interface), KERN CFS-A03
- Roller conveyor attachment, with smoothrunning, hot-dip galvanised steel rollers with ball bearings, robust aluminium profile frame, for models ≥ 30 kg [Max] with weighing plate size
- A KERN YRO-01
- **B** KERN YRO-02
- C KERN YRO-03

STANDARD											
CAL EXT KUP	KCP PROTOCOL	GLP	PCS	SUM	% PERCENT	-√+ ⊙ Ͽ) TOL	^- MOVE	<b>665</b>	B H	DMS	1 DAY
OPTION								FACTO	DRY	_	
ET RS 232	<b>USB</b>	BT 4.0	WIFI	D/A ANALOG	Ä LAN	ACCU	DAkkS +3 DAYS	ALIE		l YS	

\*Note: In addition to the RS-232 data interface, which is integrated as standard, only one other data interface can be installed and operated

Model		Weighing	Readability	Verification	Minimal	Net	Weighing	Options			
		capacity		value	load	weight	plate	Verification	DAkkS Calibr. Certificate		
		[Max]	[d]	[e]	[Min]	approx.		MIII	DAkkS		
KERN		kg	g	g	g	kg		KERN	KERN		
IFC 10K-4L	NEW	15	0,5	-	-	8	A	-	963-128		
IFC 30K-3	NEW	30	1	-	-	8	A	-	963-128		
IFC 60K-3	NEW	60	2	-	-	8	А	-	963-129		
IFC 60K-3L	NEW	60	2	-	-	11	В	-	963-129		
IFC 600K-2	NEW	600	20	-	-	44	D	-	963-130		
	Multi-division balance, with increasing or decreasing load, it switches automatically										
to the next largest or smallest weighing range [Max] and readout [d].											
IFC 30K5DM	NEW	15   30	5   10	5   10	100   200	8	A	965-228	963-128		
IFC 60K10DM	NEW	30   60	10   20	10   20	200   400	8	Α	965-229	963-129		
IFC 60K10DLM	NEW	30   60	10   20	10   20	200   400	11	В	965-229	963-129		
IFC 150K20DM	NEW	60   150	20   50	20   50	400   1000	11	В	965-229	963-129		
IFC 150K20DLM	NEW	60   150	20   50	20   50	400   1000	20	C	965-229	963-129		

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order.

The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.

# **BALANCES & TEST SERVICE 2024**

**KERN Pictograms** 





#### Internal adjusting

Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)



## Adjusting program CAL

For quick setting up of the balance's accuracy. External adjusting weight required



#### **EasyTouch**

Suitable for the connection, data transmission and control through PC or tablet



#### Memory

Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.



#### Alibi memory

Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.



#### **KERN Universal Port** (KUP)

allows the connection of external KUP interface adapters, e.g. RS-232, RS-485, SB, Bluetooth, WIFI, Analogue, Ethernet etc. for the exchange of data and control commands, without installation effort



# RS-232 Data interface

To connect the balance to a printer, PC or network



#### **RS-485 Data interface**

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



# **USB** Data interface

To connect the balance to a printer, PC or other peripherals



#### Bluetooth\* Data interface

To transfer data from the balance to a printer, PC or other peripherals



## WIFI Data interface

To transfer data from the balance to a printer, PC or other peripherals



#### **Control outputs**

(optocoupler, digital I/O) To connect relays, signal lamps, valves, etc.



#### Analogue interface

to connect a suitable peripheral device for analogue processing of the measurements



#### Interface for second balance

For direct connection of a second balance



#### **Network interface**

For connecting the scale to an Ethernet network



#### **KERN Communication** Protocol (KCP)

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



#### GLP/ISO log intern

The balance displays weight, date and time, independent of a printer connection



#### **GLP/ISO log Printer**

With weight, date and time. Only with KERN printers.



#### Piece counting

Reference quantities selectable. Display can be switched from piece to weight



#### Recipe level A

The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out



#### Recipe level B

Internal memory for complete recipés with name and target value of the recipe ingredients. User guidance through display



# Totalising level A

The weights of similar items can be added together and the total can be printed out



Percentage determination Determining the deviation in % from the target value (100 %)



# Weighing units

Can be switched to e.g. nonmetric units. See balance model. Please refer to KERN's website for more details



#### Weighing with tolerance range (Checkweighing)

Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model



#### Hold function

(Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value



#### Protection against dust and water splashes IPxx

The type of protection is shown in the pictogram

Suspended weighing

Load support with hook



#### on the underside of the balance

**Battery operation** Ready for battery opera-

tion. The battery type is



BATT

# specified for each device

Rechargeable battery pack Rechargeable set



#### Universal plug-in power supply

with universal input and optional input socket adapters for A) EU, CH, GB B) EU, CH, GB, US C) EU, CH, GB, US, AUS



230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available

Plug-in power supply



#### Integrated power supply unit

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request



#### Weighing principle Strain gauges

Electrical resistor on an elastic deforming body



#### Weighing principle Tuning fork

A resonating body is electromagnetically excited, causing it to oscillate



# Weighing principle Electromagnetic force compensation

Coil inside a permanent magnet. For the most accurate weighings



#### Weighing principle Single cell technology

Advanced version of the force compensation principle with the highest level of precision

M

#### Conformity Assessment

The time required for conformity assessment is specified in the pictogram



#### **DAkkS** calibration possible (DKD)

. The time required for DAkkS calibration is shown in days in the pictogram



#### Factory calibration (ISO)

The time required for Factory calibration is shown in days in the pictogram



#### Package shipment

The time required for internal shipping preparations is shown in days in the pictogram



#### Pallet shipment

The time required for internal shipping preparations is shown in days in the pictogram



<sup>\*</sup>The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners