



WTB9-3P2400S03

W9

**SMALL PHOTOELECTRIC SENSORS** 





## Ordering information

Туре	Part no.
WTB9-3P2400S03	1054717

Other models and accessories → www.sick.com/W9

Illustration may differ



## Detailed technical data

## **Features**

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Dimensions (W x H x D)	12.2 mm x 52.2 mm x 23.6 mm
Housing design (light emission)	Rectangular
Mounting hole	M3
Sensing range max.	98 mm
Sensing range	≤ 98 mm <sup>1)</sup>
Type of light	Visible red light
Light source	PinPoint LED <sup>2)</sup>
Light spot size (distance)	Ø 4.5 mm (75 mm)
Wave length	650 nm
Adjustment	None

 $<sup>^{1)}</sup>$  Object with 6% remission (based on standard white, DIN 5033).

<sup>&</sup>lt;sup>2)</sup> Average service life: 100,000 h at  $T_U$  = +25 °C.

## Mechanics/electronics

Supply voltage U <sub>B</sub>	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	30 mA <sup>3)</sup>
Switching output	PNP <sup>4)</sup>
Output function	Complementary
Switching mode	Light/dark switching <sup>4)</sup>
Output current I <sub>max.</sub>	$\leq$ 100 mA $^{5)}$
Response time	< 0.333 ms <sup>6)</sup>
Switching frequency	1,500 Hz <sup>7)</sup>
Connection type	Male connector M12, 4-pin
Circuit protection	A <sup>8)</sup> B <sup>9)</sup> C <sup>10)</sup>
Protection class	III
Weight	13 g
Special device	✓
Housing material	Plastic, VISTAL®
Optics material	Plastic, PMMA
Enclosure rating	IP66 IP67 IP69K
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493

 $<sup>^{1)}\,\</sup>mathrm{Limit}$  values when operated in short-circuit protected network: max. 8 A.

#### Classifications

ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904
ECLASS 7.0	27270904
ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904

 $<sup>^{2)}\,\</sup>text{May}$  not exceed or fall below  $\text{U}_{\text{V}}$  tolerances.

<sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Q = light switching.

 $<sup>^{5)}</sup>$  At and above Tu 50 °C, a max. load current of Imax. = 50 mA is permitted.

<sup>&</sup>lt;sup>6)</sup> Signal transit time with resistive load.

<sup>7)</sup> With light/dark ratio 1:1.

 $<sup>^{8)}</sup>$  A =  $V_S$  connections reverse-polarity protected.

 $<sup>^{9)}</sup>$  B = inputs and output reverse-polarity protected.

 $<sup>^{10)}</sup>$  C = interference suppression.

## WTB9-3P2400S03 | W9

SMALL PHOTOELECTRIC SENSORS

ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

## Adjustments

No adjustment possibility



3 LED indicator yellow: Status of received light beam

④ LED indicator green: power on

## Connection type




## Connection diagram

Cd-084

#### Characteristic curve

WT9-3, red light, 350 mm


% of sensing range



- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- 3 Sensing range on white, 90% remission factor


## Light spot size

WT9-3, red light, 350 mm



## Sensing range diagram


WT9-3, red light, 350 mm



- Sensing range
- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- ③ Sensing range on white, 90% remission factor

## Dimensional drawing (Dimensions in mm (inch))

## WT9-3



- ① Center of optical axis, receiver
- ② Center of optical axis, sender
- ③ Mounting hole M3 (Ø 3.1 mm)
- 4 LED indicator yellow: Status of received light beam
- ⑤ LED indicator green: power on
- 6 Connection cable 2 m
- Male connector M8, 4-pin
- Male connector M12, 4-pin

#### Recommended accessories

Other models and accessories → www.sick.com/W9

	Brief description	Туре	Part no.
Mounting bra	ckets and plates		
	Mounting bracket, steel, zinc coated, mounting hardware included	BEF-WN-W9-2	2022855
Plug connecto	ors and cables		
-	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF2A14- 050VB3XLEAX	2096235
Wes .	Head A: male connector, M12, 4-pin, straight Cable: unshielded	STE-1204-G	6009932

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

