

Johanson Product Information for VPEH202W223M1GV001E

Johanson Company: Johanson Dielectrics inc.

Product Release Date: 04 January, 2006

Deprecated P/N: 202S48W223MV4E

Web Page Link:

<https://www.johansondielectrics.com/high-voltage-mlc-capacitors>

Datasheet Date: 04-15-2024

Description: Capacitors High Voltage PME SMD ? 500V, 2225, X7R, 2,000.0V, 0.022 μ F \pm 20%, Ni/Sn (RoHS), 7" Reel Embossed Tape

Size for Capacitors (EIA): 2225

Thickness (Max): 0.160

Life Cycle Stage: Active - Production

End Band (Min):

Schedule B: 8532

End Band (Max):

ECCN: EAR99

Standard Item: 1

RoHS Compliance: Yes, RoHS 10/10

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 10

REACH: 1

Product Family: Capacitors

Length (Min): 0.215

Product Subfamily: Capacitors High Voltage PME SMD ? 500V

Length (Max): 0.235

Capacitance Value: 0.022

Width (Min): 0.240

Cap Unit of Meas: μ F

Width (Max): 0.270

Tolerance: \pm 20%

Packaging: 7" Reel Embossed Tape

Voltage: 2000.0

Operating Temp Range: -55°C to +125°C

Dielectric Temp Coefficient: X7R

Storage Temp Range (Packaged): -65°C to +125°C

Termination: 68

Storage Temp Range (Non Operating): +5°C to +40°C with RH 20% to 70%

Marking: No Mark