

Johanson Product Information for SCED502W102K4GV001E

**Johanson Company: Johanson Dielectrics inc.**

Product Release Date: 23 January, 2006

Deprecated P/N: 502R30W102KV3E-\*\*\*\*-SC

Web Page Link:

<https://www.johansondielectrics.com/ac-safety-capacitors>

Datasheet Date: 04-15-2024

Description: Capacitors Safety Caps, X1/Y2, 2211, X7R, 5000V, 1000pF±10%, Ni/Sn (RoHS), 7" Reel Embossed Tape

Size for Capacitors (EIA): 2211

Specification Number:  
UL60950,EN/UL/IEC60384-14

Life Cycle Stage: Active - Production

Thickness (Max): 0.115

Schedule B: 8532

End Band (Min):

ECCN: EAR99

End Band (Max):

RoHS Compliance: Yes, RoHS 10/10

Standard Item: 1

REACH: 1

Lead Time Typical (Weeks)\*:

\*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 10

Country of Origin: US

Product Family: Capacitors

Length (Min): 0.209

Product Subfamily: Capacitors Safety Caps

Length (Max): 0.241

Capacitance Value: 1000.000

Width (Min): 0.100

Cap Unit of Meas: pF

Width (Max): 0.120

Tolerance: ±10%

Packaging: 7" Reel Embossed Tape

Voltage: 5000.0

Operating Temp Range: -55°C to +125°C

Dielectric Temp Coefficient: X7R

Storage Temp Range (Packaged): -65°C to +125°C

Termination: 68

Marking: Required Safety Mark

Storage Temp Range (Non Operating): +5°C to +40°C with RH 20% to 70%