

CM12-08EBP-KW1

CAPACITIVE PROXIMITY SENSORS






Ordering information

Туре	Part no.
CM12-08EBP-KW1	6051029

Other models and accessories → www.sick.com/CM

Illustration may differ



Detailed technical data

Features

Housing	Cylindrical thread design
Thread size	M12 x 1
Diameter	Ø 12 mm
Sensing range S _n	0.5 mm 8 mm ¹⁾ 0.5 mm 4 mm ²⁾
Safe sensing range S _a	5.76 mm
Installation type	Non-flush / flush ³⁾
Switching frequency	15 Hz
Connection type	Cable, 4-wire, 2 m ⁴⁾
Switching output	PNP / NPN
Output function	Programmable
Output characteristic	Wire configurable ⁵⁾
Electrical wiring	DC 4-wire
Adjustment	Single teach-in button (Sensitivity) Cable (Sensitivity)
Enclosure rating	IP68 (According to EN 60529) ⁶⁾
Items supplied	Mounting nut, PA12 plastic (2x)

 $^{^{1)}}$ For non-flush installation.

²⁾ For flush mounting.

³⁾ For flush mounting, Teach-in necessary.

⁴⁾ Do not bend below 0 °C.

⁵⁾ Automatic detection.

 $^{^{6)}}$ 1.3 m water depth / 60 min.

Mechanics/electronics

Ripple ≤ 10 % ¹¹) Voltage drop ≤ 2.5 V DC ²¹) Current consumption 12 mA ³¹) Time delay before availability ≤ 120 ms Hysteresis 3% 20 % Reproducibility ≤ 5 % ⁴¹ ⁵¹ EMC According to EN 60947-5-2 ⁶¹ Continuous current Ia ≤ 200 mA Cable material PVC Conductor size 0.14 mm² Short-circuit protection ✓ Reverse polarity protection ✓ Power-up pulse protection ✓ Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm Ambient operating temperature -20 °C +85 °C Housing material Plastic Housing length 84.7 mm Thread length 46.5 mm Tightening torque, max. ≤ 1 Nm		
Voltage drop ≤ 2.5 V DC ²² Current consumption 12 mA ³) Time delay before availability ≤ 120 ms Hysteresis 3% 20 % Reproducibility ≤ 5 % ⁴¹ ⁵¹ EMC According to EN 60947-5-2 ⁵¹ Continuous current Ia ≤ 200 mA Cable material PVC Conductor size 0.14 mm² Short-circuit protection ✓ Reverse polarity protection ✓ Power-up pulse protection ✓ Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm Ambient operating temperature -20 °C +85 °C Housing material Plastic Housing length 84.7 mm Thread length 46.5 mm Tightening torque, max. ≤ 1 Nm	Supply voltage	10 V DC 36 V DC
Current consumption 12 mA ³⁾ 12 mB ³⁾ 420 ms 3 % 20 % Reproducibility ≤ 5 % ^{4) 5)} EMC According to EN 60947-5-2 ⁶⁾ Continuous current I _a ≤ 200 mA Cable material PVC Conductor size 0.14 mm² Short-circuit protection ✓ Reverse polarity protection ✓ Power-up pulse protection ✓ Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm Ambient operating temperature -20 ° C +85 ° C Ambient temperature, storage Housing material Housing length Thread length 12 mA ³⁾ 12 mA ³⁾ 12 mS ³⁾ 13 mS ³ 15 mS ³ 16 mS ³ 17 mS ³ 18 mS ³ 19 mS ³ 10 mS ³ 11 mS / 10 55 Hz, 1 mm -40 ° C +85 ° C Ambient temperature, storage 40 ° C +85 ° C Housing material Housing length 46.5 mm 15 intending torque, max.	Ripple	≤ 10 % ¹⁾
Time delay before availability Hysteresis Reproducibility \$5 \% \alpha^{4} \5) EMC According to EN 60947-5-2 \(\text{ 6} \) Continuous current Ia \$200 mA Cable material PVC Conductor size 0.14 mm² Short-circuit protection #Reverse polarity protection Vererup pulse protection Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm Ambient operating temperature -20 \circ C +85 \circ C Ambient temperature, storage Housing material Housing length 1	Voltage drop	\leq 2.5 V DC $^{2)}$
Hysteresis Reproducibility ≤5% ^{4) 5)} EMC According to EN 60947-5-2 ⁶⁾ Continuous current I _a ≤200 mA PVC Conductor size 0.14 mm² Short-circuit protection ✓ Reverse polarity protection ✓ Power-up pulse protection ✓ Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm Ambient operating temperature -20 °C +85 °C Ambient temperature, storage Housing material Housing length Thread length Tightening torque, max.	Current consumption	12 mA ³⁾
Reproducibility	Time delay before availability	≤ 120 ms
EMC Continuous current Ia ≤ 200 mA Cable material PVC Conductor size 0.14 mm² Short-circuit protection ✓ Reverse polarity protection ✓ Power-up pulse protection Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm Ambient operating temperature -20 °C +85 °C Ambient temperature, storage +00 °C +85 °C Housing material Plastic Housing length 84.7 mm Thread length 46.5 mm ≤ 1 Nm	Hysteresis	3 % 20 %
Continuous current I _a ≤ 200 mA Cable material PVC Conductor size 0.14 mm² Short-circuit protection ✓ Reverse polarity protection ✓ Power-up pulse protection ✓ Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm Ambient operating temperature -20 °C +85 °C Ambient temperature, storage +40 °C +85 °C Housing material Plastic Housing length 84.7 mm Thread length 46.5 mm ≤ 1 Nm	Reproducibility	≤ 5 % ^{4) 5)}
Cable material Conductor size 0.14 mm² Short-circuit protection ✓ Reverse polarity protection ✓ Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm Ambient operating temperature -20 °C +85 °C Ambient temperature, storage Housing material Housing length Thread length Tightening torque, max. PVC 0.14 mm² ✓ 1.15 mm² ✓ 1.15 mm² ✓ 1.15 mm²	EMC	According to EN 60947-5-2 ⁶⁾
Conductor size Short-circuit protection Reverse polarity protection ✓ Power-up pulse protection Shock and vibration resistance Ambient operating temperature -20 °C +85 °C Ambient temperature, storage Housing material Housing length Thread length Tightening torque, max. 0.14 mm² 0.14 mm	Continuous current I _a	≤ 200 mA
Short-circuit protection Reverse polarity protection Power-up pulse protection Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm -20 °C +85 °C Ambient temperature, storage -40 °C +85 °C Housing material Housing length Thread length Tightening torque, max. ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓	Cable material	PVC
Reverse polarity protection Power-up pulse protection Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm -20 °C +85 °C Ambient operating temperature -20 °C +85 °C Housing material Plastic Housing length 84.7 mm Tightening torque, max. ✓ 1 Nm	Conductor size	0.14 mm ²
Power-up pulse protection Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm -20 °C +85 °C Ambient temperature, storage -40 °C +85 °C Housing material Housing length Thread length 46.5 mm ≤1 Nm	Short-circuit protection	√
Shock and vibration resistance 30 g, 11 ms / 10 55 Hz, 1 mm -20 °C +85 °C Ambient temperature, storage -40 °C +85 °C Housing material Plastic Housing length 84.7 mm Thread length 46.5 mm ≤ 1 Nm	Reverse polarity protection	✓
Ambient operating temperature -20 °C +85 °C Ambient temperature, storage -40 °C +85 °C Housing material Plastic Housing length 84.7 mm Thread length 46.5 mm Tightening torque, max. ≤1 Nm	Power-up pulse protection	✓
Ambient temperature, storage -40 °C +85 °C Housing material Plastic Housing length 84.7 mm Thread length 46.5 mm Tightening torque, max. ≤1 Nm	Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
Housing material Plastic Housing length 84.7 mm Thread length 46.5 mm Tightening torque, max. ≤ 1 Nm	Ambient operating temperature	-20 °C +85 °C
Housing length 84.7 mm Thread length 46.5 mm Tightening torque, max. ≤ 1 Nm	Ambient temperature, storage	-40 °C +85 °C
Thread length 46.5 mm Tightening torque, max. ≤ 1 Nm	Housing material	Plastic
Tightening torque, max. ≤ 1 Nm	Housing length	84.7 mm
	Thread length	46.5 mm
UL File No. NRKH.E191603	Tightening torque, max.	≤ 1 Nm
	UL File No.	NRKH.E191603

¹⁾ Of Ub.

Safety-related parameters

MTTF _D	603 years
DC _{avg}	0 %
T _M (mission time)	20 years

Reduction factors

Note	The values are reference values which may vary
Metal	1
Water	1
PVC	Approx. 0.4
Oil	Approx. 0.25
Glass	0.6
Ceramics	0.5

²⁾ At I_a max.

³⁾ Without load.

⁴⁾ Of Sr.

⁵⁾ Supply voltage Ub and constant ambient temperature Ta.

⁶⁾ For non-flush installation min. 1 x Sn and sensor grounded.

CM12-08EBP-KW1 | CM

CAPACITIVE PROXIMITY SENSORS

Alcohol	0.7
Wood	0.2 0.7

Installation note


Remark	Associated graphic see "Installation"
A	8 mm
В	12 mm
c	12 mm
D	12 mm
E	8 mm
F	6 x S _n (max. 48 mm)


Classifications

eCl@ss 5.0	27270102
eCl@ss 5.1.4	27270102
eCl@ss 6.0	27270102
eCl@ss 6.2	27270102
eCl@ss 7.0	27270102
eCl@ss 8.0	27270102
eCl@ss 8.1	27270102
eCl@ss 9.0	27270102
eCl@ss 10.0	27270102
eCl@ss 11.0	27270102
eCl@ss 12.0	27274201
ETIM 5.0	EC002715
ETIM 6.0	EC002715
ETIM 7.0	EC002715
ETIM 8.0	EC002715
UNSPSC 16.0901	39122230

Installation note

Non-flush installation






Connection diagram

Cd-236




Response diagram

CM12



Dimensional drawing (Dimensions in mm (inch))

CM12, cable



① LED yellow: output active; LED green: Power and signal reserve

Recommended accessories

Other models and accessories → www.sick.com/CM

	Brief description	Туре	Part no.	
Universal bar	Universal bar clamp systems			
	Plate N05 for universal clamp bracket, M12, Zinc plated steel (sheet), Zinc die cast (clamping bracket), Universal clamp (5322626), mounting hardware	BEF-KHS-N05	2051611	
Mounting brackets and plates				
	Mounting plate for M12 sensors, steel, zinc coated, without mounting hardware	BEF-WG-M12	5321869	
40	Mounting bracket for M12 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M12	5308447	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

