

UM12-1172261 UM12

ULTRASONIC SENSORS





Ordering information

Туре	Part no.
UM12-1172261	6053544

Other models and accessories → www.sick.com/UM12



Detailed technical data

Mechanics/electronics

Supply voltage V _s	DC 10 V 30 V ¹⁾	
Power consumption	\leq 0.9 W ²⁾	
Initialization time	< 300 ms	
Design	Cylindrical	
Housing material Metal (nickel-plated brass, PBT, ultrasonic transducer: polyurethane foam,		
Thread size	M12 x 1	
Connection type	Male connector, M12, 4-pin	
Indication	2 x LED	
Weight	15 g	
Sending axis	Straight	
Dimensions (W x H x D)	12 mm x 12 mm x 60.1 mm	
Enclosure rating	IP65 / IP67	
Protection class	III	

 $^{^{1)}}$ Limit values, reverse-polarity protected Operation in short-circuit protected network: max. 8 A, class 2.

Safety-related parameters

MTTF _D	101 years
DC _{avg}	0%

Performance

Operating range, limiting range	20 mm 150 mm, 250 mm
Target	Natural objects
Resolution	≥ 0.069 mm
Repeatability	± 0.15 % ¹⁾
Accuracy	± 1 % ²⁾

 $^{^{1)}}$ In relation to the current measured value, minimum value \geq resolution.

²⁾ Without load.

 $^{^{2)}}$ Referring to current measurement value.

 $^{^{3)}}$ Subsequent smoothing of the analog output, depending on the application, may increase the response time by up to 200 %.

⁴⁾ Functions may vary depending on sensor type.

Temperature compensation	J.
Response time	24 ms ³⁾
Output time	8 ms
Ultrasonic frequency (typical)	380 kHz
Additional function	Teach-in of analog output Invertable analog output Reset to factory default $^{4)}$

 $^{^{1)}}$ In relation to the current measured value, minimum value \geq resolution.

Interfaces

Analog output	
Number	1
Туре	Current output
Current	4 mA 20 mA, \leq 500 $\Omega^{1)}$
Resolution	12 bit

 $^{^{1)}}$ For 4 mA ... 20 mA and Vs \leq 20 V max. load \leq 100 $\Omega.$

Ambient data

Ambient temperature, operation	-25 °C +70 °C
Ambient temperature, storage	-40 °C +85 °C

Classifications

ECLASS 5.0	27270804
ECLASS 5.1.4	27270804
ECLASS 6.0	27270804
ECLASS 6.2	27270804
ECLASS 7.0	27270804
ECLASS 8.0	27270804
ECLASS 8.1	27270804
ECLASS 9.0	27270804
ECLASS 10.0	27270804
ECLASS 11.0	27270804
ECLASS 12.0	27272806
ETIM 5.0	EC001846
ETIM 6.0	EC001846
ETIM 7.0	EC001846
ETIM 8.0	EC001846
UNSPSC 16.0901	41111960


²⁾ Referring to current measurement value.

 $^{^{3)}}$ Subsequent smoothing of the analog output, depending on the application, may increase the response time by up to 200 %.

⁴⁾ Functions may vary depending on sensor type.

Dimensional drawing (Dimensions in mm (inch))

UM12-11x2261, UM12-11x2271



- ① Connection
- ② Mounting nuts, SW 17 mm
- 3 Status display supply voltage active (green), switching and analog output (orange)

Connection type




Connection diagram

UM12-11x2261, UM12-11x2271

Detection area

UM1x-x17

Detection area in mm (inch)



- $\textcircled{1} \ \ \, \text{Detection range dependent on reflection properties, size, and alignment of the object}$
- ② Limiting range
- ③ Operating range
- 4 Example object: aligned plate 500 mm x 500 mm
- ⑤ Example object: cylindrical bar with a diameter of 10 mm

Recommended accessories

Other models and accessories \rightarrow www.sick.com/UM12

	Brief description	Туре	Part no.	
Mounting bra	Mounting brackets and plates			
	Mounting plate for M12 sensors, steel, zinc coated, without mounting hardware	BEF-WG-M12	5321869	
Plug connectors and cables				
	 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 2 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A14- 020VB3XLEAX	2096234	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

