



WS/WE24-2B440 W24

COMPACT PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WS/WE24-2B440	1017875

Other models and accessories → www.sick.com/W24

Illustration may differ



Detailed technical data

Features

Functional principle	Through-beam photoelectric sensor
Dimensions (W x H x D)	27 mm x 87.5 mm x 65 mm
Housing design (light emission)	Rectangular
Sensing range max.	0 m 60 m
Sensing range	0 m 50 m
Focus	Approx. 1°
Type of light	Visible red light
Light source	LED ¹⁾
Light spot size (distance)	Ø 700 mm (50 m)
Angle of dispersion	Approx. 1°
Adjustment	Potentiometer

 $^{^{1)}}$ Average service life: 100,000 h at T_U = +25 °C.

Mechanics/electronics

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Power consumption, sender	50 mA ³⁾

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.

 $^{^{4)}}$ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

⁶⁾ A = V_S connections reverse-polarity protected.

⁷⁾ C = interference suppression.

 $^{^{\}rm 8)}$ D = outputs overcurrent and short-circuit protected.

⁹⁾ Reference voltage: 50 V DC.

 $^{^{10)}}$ Static, low heat output, use in +5 ° C ... +15 ° C.

Power consumption, receiver	50 mA ³⁾
Switching output	NPN, PNP
Switching mode	Light/dark switching
Switching mode selector	Selectable via PNP/NPN selector, selectable via light/dark selector
Output current I _{max.}	≤ 100 mA
Response time	≤ 500 µs ⁴⁾
Switching frequency	1,000 Hz ⁵⁾
Angle of reception	Approx. 2.5°
Time functions	On delayoff delay
Delay time	Adjustable via time delay selector switch, 0.5 s 10 s
Connection type	Male connector M12, 4-pin
Circuit protection	A ⁶⁾ C ⁷⁾ D ⁸⁾
Protection class	и ⁹⁾
Weight	660 g
Front screen heating	✓ ¹⁰⁾
Housing material	Metal, zinc diecast
Optics material	Plastic, PMMA
Enclosure rating	IP69K
Test input sender off	TE to 0 V
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493
Part number of individual components	2021418 WE24-2B440 2021465 WS24-2D440

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

Safety-related parameters

MTTF _D	392 years
DC _{avg}	0 %
T _M (mission time)	20 years

Classifications

ECLASS 5.0	27270901
ECLASS 5.1.4	27270901
ECLASS 6.0	27270901

 $^{^{2)}\,\}mbox{May}$ not exceed or fall below $\mbox{U}_{\mbox{\scriptsize V}}$ tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ A = V_S connections reverse-polarity protected.

⁷⁾ C = interference suppression.

 $^{^{8)}}$ D = outputs overcurrent and short-circuit protected.

⁹⁾ Reference voltage: 50 V DC.

 $^{^{10)}}$ Static, low heat output, use in +5 $^{\circ}$ C ... +15 $^{\circ}$ C.


WS/WE24-2B440 | W24

COMPACT PHOTOELECTRIC SENSORS

ECLASS 6.2	27270901
ECLASS 7.0	27270901
ECLASS 8.0	27270901
ECLASS 8.1	27270901
ECLASS 9.0	27270901
ECLASS 10.0	27270901
ECLASS 11.0	27270901
ECLASS 12.0	27270901
ETIM 5.0	EC002716
ETIM 6.0	EC002716
ETIM 7.0	EC002716
ETIM 8.0	EC002716
UNSPSC 16.0901	39121528

Adjustments

WT24-2, WL24-2, WS/WE24-2, DC, with time functions




- ② LED signal strength indicator
- Sensitivity control
- Light/dark selector
- NPN/PNP changeover switch
- 1 Time control t_2 = OFF delay
- 2 Time control t_1 = ON delay
- Time delay selector switch

Connection type



Connection diagram

Cd-118




- ② Receiver

Characteristic curve


WS/WE24-2






Sensing range diagram

WS/WE24-2



Dimensional drawing (Dimensions in mm (inch))

WS/WE24-2



- ① Alignment sight
- ② LED signal strength indicator
- 3 Center of optical axis
- ④ M5 threaded mounting hole, 6 mm deep
- ⑤ M5 threaded mounting hole, through-hole
- $\ \, \textbf{\textcircled{6}} \,\,$ M16 screw fixing and plug rotatable by 90 $^{\circ}$

Recommended accessories

Other models and accessories → www.sick.com/W24

	Brief description	Туре	Part no.
Mounting brackets and plates			
	Mounting bracket, large, stainless steel, without mounting hardware for the sensor	BEF-WG-W24	4026324
Plug connectors and cables			
	 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A14- 050VB3XLEAX	2096235
	 Connection type head A: Male connector, M12, 4-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² 	STE-1204-G	6009932

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

