



WS/WE24-2S01

**COMPACT PHOTOELECTRIC SENSORS** 





#### **Ordering information**

Туре	Part no.
WS/WE24-2S01	1023549

Other models and accessories → www.sick.com/W24

Illustration may differ



#### Detailed technical data

#### **Features**

Functional principle	Through-beam photoelectric sensor
Dimensions (W x H x D)	27 mm x 87.5 mm x 65 mm
Housing design (light emission)	Rectangular
Sensing range max.	0 m 60 m
Sensing range	0 m 50 m
Focus	Approx. 1°
Type of light	Visible red light
Light source	LED <sup>1)</sup>
Light spot size (distance)	Ø 700 mm (50 m)
Angle of dispersion	Approx. 1°
Adjustment	Potentiometer
Alarm output	✓
Special features	Dynamic front lense heating Front lense made of glass

 $<sup>^{1)}</sup>$  Average service life: 100,000 h at TU = +25 °C.

### Mechanics/electronics

Supply voltage U <sub>B</sub>	10 V DC 30 V DC <sup>1)</sup>

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

 $<sup>^{2)}\,\</sup>mathrm{May}$  not exceed or fall below  $\mathrm{U}_{\mathrm{V}}$  tolerances.

<sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Signal transit time with resistive load.

<sup>5)</sup> With light/dark ratio 1:1.

 $<sup>^{6)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

<sup>&</sup>lt;sup>7)</sup> C = interference suppression.

 $<sup>^{8)}</sup>$  D = outputs overcurrent and short-circuit protected.

<sup>9)</sup> Reference voltage: 50 V DC.

<sup>10)</sup> Dynamic, high heat output, application for quickly changing temperatures between -5° C ... +10° C, Front screen material: Glass.

Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Power consumption, sender	$\leq$ 150 mA $^{3)}$
Power consumption, receiver	$\leq$ 140 mA $^{3)}$
Switching output	NPN, PNP
Switching mode	Light/dark switching
Switching mode selector	Selectable via PNP/NPN selector, selectable via light/dark selector
Output current I <sub>max.</sub>	≤ 100 mA
Response time	≤ 500 μs <sup>4)</sup>
Switching frequency	1,000 Hz <sup>5)</sup>
Angle of reception	Approx. 2.5°
Connection type	Male connector M12, 5-pin
Circuit protection	A <sup>6)</sup> C <sup>7)</sup> D <sup>8)</sup>
Protection class	
Weight	700 g
Front screen heating	<b>✓</b> <sup>10)</sup>
Housing material	Metal, zinc diecast
Optics material	Glass, glass
Enclosure rating	IP67
Test input sender off	TE to 0 V
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
Part number of individual components	2026925 WS24-2D530S01 2026926 WE24-2V530S01

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

## Safety-related parameters

MTTF <sub>D</sub>	423 years
DC <sub>avg</sub>	0 %

#### Classifications

ECLASS 5.0	27270901
ECLASS 5.1.4	27270901
ECLASS 6.0	27270901
ECLASS 6.2	27270901

 $<sup>^{2)}</sup>$  May not exceed or fall below  $\mathrm{U}_{\mathrm{V}}$  tolerances.

<sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Signal transit time with resistive load.

 $<sup>^{5)}</sup>$  With light/dark ratio 1:1.

 $<sup>^{6)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

<sup>&</sup>lt;sup>7)</sup> C = interference suppression.

<sup>8)</sup> D = outputs overcurrent and short-circuit protected.

 $<sup>^{9)}</sup>$  Reference voltage: 50 V DC.

 $<sup>^{10)}</sup>$  Dynamic, high heat output, application for quickly changing temperatures between  $-5\,^{\circ}$  C ...  $+10\,^{\circ}$  C, Front screen material: Glass.


# WS/WE24-2S01 | W24

## COMPACT PHOTOELECTRIC SENSORS

ECLASS 7.0	27270901
ECLASS 8.0	27270901
ECLASS 8.1	27270901
ECLASS 9.0	27270901
ECLASS 10.0	27270901
ECLASS 11.0	27270901
ECLASS 12.0	27270901
ETIM 5.0	EC002716
ETIM 6.0	EC002716
ETIM 7.0	EC002716
ETIM 8.0	EC002716
UNSPSC 16.0901	39121528

### Adjustments

WT24-2, WL24-2, WS/WE24-2, DC




- ② LED signal strength indicator
- Adjustment sensing range (WT) / sensitivity (WL, WS/WE)
   Light/dark selector
- ② NPN/PNP changeover switch

### Connection type



### Connection diagram

#### Cd-119




SenderReceiver

#### Characteristic curve


WS/WE24-2

#### Function reserve




### Sensing range diagram

#### WS/WE24-2



### Dimensional drawing (Dimensions in mm (inch))

WS/WE24-2



- ① Alignment sight
- ② LED signal strength indicator
- 3 Center of optical axis
- ④ M5 threaded mounting hole, 6 mm deep
- ⑤ M5 threaded mounting hole, through-hole
- $\ \, \textbf{\textcircled{6}} \,\,$  M16 screw fixing and plug rotatable by 90  $^{\circ}$

#### Recommended accessories

Other models and accessories → www.sick.com/W24

	Brief description	Туре	Part no.
Mounting bra	ckets and plates		
	Mounting bracket, large, stainless steel, without mounting hardware for the sensor	BEF-WG-W24	4026324
Plug connecto	ors and cables		
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A15- 050VB5XLEAX	2096240

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

