



Part Number : [1053001810](#)

Product Description : Nano-Fit Crimp Terminal, Female, 0.025µm Gold (Au) Plating, 24-26 AWG

Series Number : 105300

Status : Active

Product Category : Crimp Terminals

Documents & Resources

Drawings

[Drawing 1053001810_sd.pdf](#)

[Packaging Design Drawing PK-105300-100-000.pdf](#)

Specifications

[Product Specification PS-105300-100-001.pdf](#)


[Product Specification 2014471000-PS-000.pdf](#)

[Product Specification 2192681000-PS-000.pdf](#)

[Test Summary 2014471000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Crimp Terminals
Series	105300
Description	Nano-Fit Crimp Terminal, Female, 0.025µm Gold (Au) Plating, 24-26 AWG
Application	Power, Wire-to-Board, Wire-to-Wire
Product Family	Nano-Fit Power Connectors
Product Name	Nano-Fit,Nano-Fit BMI
UPC	196823536571

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Durability (mating cycles max)	50
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.095/g
Packaging Type	Reel
Plating min - Mating	0.025µm
Plating min - Termination	1.250µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30mm
Wire Size (AWG)	24, 26
Wire Size mm ²	N/A

Use with Part(s)

Description	Part Number
Nano-Fit TPA Capable Single Row Receptacle Housings	<u>105307</u>
Nano-Fit TPA Capable Dual Row Receptacle Housings	<u>105308</u>
Nano-Fit BMI Dual Row Receptacle Housings	<u>219268</u>
Nano-Fit BMI TPA Capable Plug Housings	<u>224556</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Nano-Fit Receptacle Terminals, 24 AWG and 26 AWG, UL1061 and UL1007 Insulations	<u>638276000</u>
Extraction Tool for Nano-Fit Power Connectors and Crimp Terminals, 20-26 AWG	<u>638244600</u>
FineAdjust Applicator for Insulation OD 1.20-1.45mm - UL1007	<u>639034800</u>
FineAdjust Applicator for Insulation OD 0.90-1.15mm - UL1061	<u>639032500</u>
