

Johanson Product Information for QSCT251Q330J1GV001E

Johanson Company: Johanson Technology inc. Product Release Date: 03 January, 2006

Deprecated P/N: 251R15S330JV4E

Datasheet Date: 04-10-2024

Description: Capacitors High-Q MLC S-Series, 0805, Hi-Q NP0/C0G, 250V, 33pF±5%, Ni/Sn (RoHS), 7" Reel Embossed Tape

Life Cycle Stage: Active - Production

Schedule B: 8532

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: US

Product Family: Capacitors

Product Subfamily: Capacitors High-Q MLC S-Series

Capacitance Value: 33.000

Cap Unit of Meas: pF

Tolerance: ±5%

Voltage: 250.0

Dielectric Temp Coefficient: Hi-Q NP0/C0G

Termination: 68

Marking: No Mark

Web Page Link:

<https://www.johansontechnology.com/R15S>

Size for Capacitors (EIA): 0805

Specification Number: 35S0118E

Thickness (Max): 0.046

Thickness (Min): 0.034

End Band (Min):

End Band (Max):

Standard Item: 1

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 8

Length (Min): 0.072

Length (Max): 0.088

Width (Min): 0.042

Width (Max): 0.058

Packaged Weight (lb) Arm: 0.30

Packaging: 7" Reel Embossed Tape

Packaging Qty: 4000

Operating Temp Range: -55°C to +150°C

Storage Temp Range (Packaged): -65°C to +150°C



Storage Temp Range (Non Operating): +5°C to +40°C with RH 20% to 70%