

Applications

- LED Lighting System
- PLC network adapters
- AC Line Power Supplies
- AC/DC power supplies
- Modem Power Supply
- White goods, appliances, industrial controls

**RoHS
Compliant**

Features

- IEC61000-4-2 – Electrostatic discharge immunity test
- IEC61000-4-4 – Electrical fast transient/burst immunity test
- IEC61000-4-5 – Surge immunity test
- Over Current Protection
- Over Voltage Protection
- Prevent thermal runaway Occurs


Specification

Maximum Continuous Operating Voltage : 240VAC
 Maximum Limited Duration Voltage : 400VAC~600VAC
 Maximum Limited Duration Current : 10A~40A
 Temperature Range : -40°C to 85°C

Material

Lead material : Tin plated copper, 22 AWG.
 Soldering characteristics : MIL-STD-202, Method 208E.
 Insulating coating : Flame retardant epoxy, meets UL-94V-0 requirement.

Electrical Schematic




Overcurrent(terminals 1-2) Electrical Characteristics (23°C)

Part Number	Hold Current (A)	Trip Current (A)	Time to Trip			Resistance		
			Current (A)	Typ. Time (Sec)	Max. Time (Sec)	R _{MIN} Ohms	R _{MAX} Ohms	R _{1MAX} Ohms
MCMOV10271-T015	0.15	0.3	1	0.9	3	6.5	14	16
MCMOV10431-T015								
MCMOV14431-T035	0.35	0.75	3	0.5	2	1.4	2.2	2.8
MCMOV14431-T075	0.75	1.5	7	0.9	1.2	0.37	0.8	1

Overcurrent(terminals 2-3) Electrical Characteristics (23°C)

Part Number	Varistor Voltage V@1mA		DC Resistance @100V MΩ	Maximum Clamping Voltage @25A V DC	Typical Power Pd, W
	V DC	Tolerance			
MCMOV10271-T015	260	+14% / -7%	>10	455	0.25
MCMOV10431-T015	430	+10% / -10%		710	
MCMOV14431-T035					0.6
MCMOV14431-T075					


Product Dimensions



Part Number	Figure	A	B	C	D		E	F
		Maximum	Maximum	Maximum	Min	Max	Nominal	Maximum
MCMOV10271-T015	1	12	15	6.6	6	--	2.5	12
MCMOV10431-T015	2		17		8.5	11.5	5.1	
MCMOV14431-T035	2	16	21	7.4	3	5	2.5	--
MCMOV14431-T075	3						2.5	


Typical Time-To-Trip at 23°C

A = MCMOV10271-T015
 A = MCMOV10431-T015
 B = MCMOV14431-T035
 C = MCMOV14431-T075




Impulse Life Time Rating Curve

MCMOV10 Series




MCMOV14 Series




V-I Curves

- A = MCMOV10271-T015
- B = MCMOV10431-T015
- C = MCMOV14431-T035
MCMOV14431-T075



B
A



C

Part Number Table

Description	Part Number
Circuit Protected MOV, 260V DC, 0.15A	MCMOV10271-T015
Circuit Protected MOV, 430V DC, 0.15A	MCMOV10431-T015
Circuit Protected MOV, 430V DC, 0.35A	MCMOV14431-T035
Circuit Protected MOV, 430V DC, 0.75A	MCMOV14431-T075

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.