



SAFETY SYSTEMS FOR AGVS AND AMRS



FX0-GETC00000 | Safe EFI-pro System

SAFETY SYSTEMS FOR AGVS AND AMRS



Ordering information

Fieldbus, industrial network	Туре	Part no.
EtherCAT [®]	FX0-GETC00000	1051432

Other models and accessories -> www.sick.com/Safe_EFI-pro_System




Detailed technical data

Features	
Module	Gateway
Fieldbus, industrial network	EtherCAT®
Configuration method	Via software (Flexi Soft Designer, Safe EFI-pro System: Safety Designer)
Interfaces	
Fieldbus, industrial network	EtherCAT®
Data transmission rate	10 Mbit/s, 10Base-T 100 Mbit/s, 100Base-T autosensing
Connection type	2 x female connector, RJ-45
Electrical data	
Protection class	III (EN 61140)
Voltage supply	Via FLEXBUS+
Internal power consumption	\leq 3 W ¹⁾
¹⁾ Via FLEXBUS+.	
Mechanical data	
Dimensions (W x H x D)	22.5 mm x 96.5 mm x 120.6 mm
Weight	150 g (± 10 %)
Ambient data	
Enclosure rating	IP20 (EN 60529)
Ambient operating temperature	-25 °C +55 °C
Storage temperature	-25 °C +70 °C
Air humidity	≤ 95 %, Non-condensing
Classifications	
ECLASS 5.0	27243001

ECLASS 5.1.4	27243101
ECLASS 6.0	27243101
ECLASS 6.2	27243101
ECLASS 7.0	27243101
ECLASS 8.0	27243101
ECLASS 8.1	27243101
ECLASS 9.0	27243101
ECLASS 10.0	27243101
ECLASS 11.0	27243101
ECLASS 12.0	27243101
ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449
ETIM 8.0	EC001449
UNSPSC 16.0901	32151705

Dimensional drawing (Dimensions in mm (inch))

FXO-GETC



FX0-GETC00000 | Safe EFI-pro System

SAFETY SYSTEMS FOR AGVS AND AMRS

Recommended accessories

Other models and accessories -> www.sick.com/Safe_EFI-pro_System

	Brief description	Туре	Part no.
Others			
	 Sub product family: SIM1000 FX Product category: Programmable devices Supported products: 2D and 3D LiDAR sensors, pico- und midiCam series, incremental and absolute encoders, Image-based code readers, Fixed mount barcode scanners, RFID read/write device, displacement measurement sensors, Photoelectric sensors, Flexi Soft main module Processor: Dual-core ARM Cortex-A9 CPU with NEON accelerator Toolkit: SICK algorithm API Further functions: FPGA for I/O handling Connections: Terminal block 1-4, Ethernet, FLEXBUS+ Enclosure rating: IP20 	SIM1000-0P0B110	1097817
Safety switc	hing amplifier		
	 Applications: Output expansion module for OSSDs Compatible sensor types: Safety sensors with OSSDs Connection type: Front connector with spring terminals Restart interlock: no External device monitoring (EDM): Via path Outputs: 2 enabling current paths (safe), 1 feedback current path (for use as external device monitoring, not safe) Housing width: 18 mm 	RLY3-OSSD100	1085343
	 Applications: Output expansion module for OSSDs Compatible sensor types: Safety sensors with OSSDs Connection type: Front connector with spring terminals Restart interlock: no External device monitoring (EDM): Via path Outputs: 4 enabling current paths (safe), 1 feedback current path (for use as external device monitoring, not safe), 1 signaling current path (not safe) Housing width: 28 mm 	RLY3-OSSD400	1099971

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

