

Product information

35 52 145 ESD

Electronics Pliers ESD

DIN ISO 9655 DIN EN 61 340-5



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools



General

Article No.	35 52 145 ESD
EAN	4003773089223
Pliers	mirror polished
Head	mirror polished
Handles	with multi-component grips
Weight	86 g
Dimensions	145 x 66 x 17 mm
Standard	DIN ISO 9655 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw length (B)	34.1 mm
Jaw thickness (joint) (D)	8.5 mm
Tips width (E)	2.5 mm
Tips thickness (F)	1.8 mm
Head width (A)	13.0 mm
ESD	yes

technical change and errors excepted