

Data Sheet SMT-0827-T-HT-R

PUI Audio's **High-Temp** line of products is designed to meet and exceed the needs of the automotive industry with ultra-wide operating temperatures. The **SMT-0827-T-HT-R** is designed for high output at 2700 Hz in a small package.


Features:

- Wide operating temperature range of -40° C $\sim +105^{\circ}$ C
- Weighs only 0.4 grams
- High 95 dBA minimum output @ 10cm


Specifications

Parameters	Values	Units
Rated Voltage	3.6	V0-p
Operating Voltage Range	2 ~ 5	V0-p
Current Draw at Rated Voltage	≤100	mA
Coil Resistance	15±3	Ohms
Minimum SPL @ 10cm	≥95	dBA
Resonant Frequency	2700 ±500	Hz
Housing Material	LCP	-
Weight	0.4	Grams
Acceptable Soldering Methods	Hand Solder, Reflow Solder	See page 2 for soldering information
Environmental Compliances	RoHS	-
Storage Temperature	-40 ~ +120	°C
Operating Temperature	-40 ~ +105	°C


Measurement Method (3.6V0-p, 2700Hz, 50% duty cycle square wave with a SPL meter at 10cm)



Typical Frequency Response (3.6 V0-p sine-sweep with microphone spaced at 10cm)



Recommended Soldering Procedure




Profile Feature	Pb-Free Assembly
Average ramp-up rate(T _L to Tp)	3℃/second max.
Preheat	
-Temperature Min.(Ts _{min})	150℃
-Temperature Min.(Ts _{max})	200℃
-Temperature Min.(ts)	60∼180 seconds
Tsmax to TL	
-Ramp-up Rate	3℃/second max.
Time maintained above:	
- Temperature(T _L)	217°C
-Time(T _L)	60∼150 seconds
Peak temperature(Tp)	250℃+0/-5℃
Time within 5°C of actual Peak temperature (tp)	6 seconds max.
Ramp-down Rate	6℃/second max.
Time 25℃ to Peak Temperature	8 minutes max.

Reliability Testing


Type of Test	Test Specifications
High Temperature Test	The part shall be capable of withstanding a storage temperature of +120°C for 120 hours
Low Temperature Test	The part shall be capable of withstanding a storage temperature of -40°C for 120 hours
Humidity Test	40±2°C, 90∼95% RH, 120 hours
Temperature Cycle Testing	Total 5 cycles, 1 cycle consisting of: -40±2°C, 30 minutes 20±5°C, 15 minutes 120±2°C, 30 minutes 20±5°C, 15 minutes
Vibration Test	The part shall be subjected to a vibration cycle of 10Hz in a period of 1 minute. Total peak amplitude shall be 1.52mm (9.3g). The vibration test shall consist of 2 hours per plane in each three mutually perpendicular planes for a total time of 6 hours.
Shock Test	Sounder shall be measured after being applied a shock (980m/s ²) for each three mutually perpendicular directions to each of 3 times by a half sine wave.
Drop Test	Dropped from 700mm onto the surface of a 10mm thick wooden board. Applied to the top and side of the part.

 $^{2\} hours$ after the test the part shall meet specifications without any degradation in appearance and performance except SPL shall be within $\pm 10\ dB$ of initial value.

$\textbf{Dimensions} \ (\textbf{If polarity needs to be observed, mention it here and call out location of positive pin/pad)}$




Suggested Land Pattern*



*This land pattern is advisory only and its use or adaptation is entirely voluntary. PUI Audio disclaims all liability of any kind associated with the use, application, or adaptation of this land pattern.

Packaging



- NOTE:
 - 1.10 sprocket hole pitch cumulative tolerance +/-0.20mm.
 - 2.All dimensions meet EIA-481-D requirements.
 - 3.Thickness: 0.4+/-0.05mm.

No Components

150mm

4.Component loaded per 13"reel: 1000pcs.

A 8:1 2.3 24.4 0

One of the content of the content

No Components

0 400mm


Start

User Direction of Feed

Components

Empty component Pockets sealed With cover tape

Packaging Cont'd



NOTES:

- 1.1000 PCS per box
- 2.Total 10 boxes per carton
- 3.Total 10000 PCS carton

This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2020, PUI Audio Inc.

Specifications Revisions

Revision	Description	Date
-	Released from Engineering	4/1/20

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- 2. Specifications subject to change or withdrawal without notice.