

Data Sheet SMT-1027-S-HT-2-R


PUI Audio's **High-Temp** line of products is designed with ultra-wide operating temperatures. The **SMT-1027-S-HT-2-R** is built for high output at 2700 Hz in a small package.

- 95 dB @ 10cm minimum output
- Wide operating temperature range of -40°C \sim +105°C
- Only weighs 0.6 grams

Specifications


Parameters	Values	Units
Rated Voltage	3.6	V0-p
Operating Voltage Range	2 ~ 5	V0-p
Current Draw at Rated Voltage	≤100	mA
Coil Resistance	18±3	Ohms
Minimum SPL @ 10cm	≥95	dBA
Resonant Frequency	2700 ± 500	Hz
Housing Material	LCP	-
Weight	0.6	Grams
Acceptable Soldering Methods	Hand Solder, Reflow Solder	See page 2 for soldering information
Environmental Compliances	RoHS	-
Storage Temperature	-40 ~ +120	°C
Operating Temperature	-40 ~ +105	°C

$\textbf{Measurement Method}_{\text{(3.6V0-p, 2700Hz, 50\% duty cycle square wave with a SPL meter at 10cm)}}$




©2020, PUI Audio Inc.

Typical Frequency Response (3.6 V0-p sine-sweep with microphone spaced at 10cm)



Recommended Soldering Procedure




111	
Profile Feature	Pb-Free Assembly
Average ramp-up rate(T _L to Tp)	3℃/second max.
Preheat	
-Temperature Min.(Ts _{min})	150℃
-Temperature Min.(Ts _{max})	200℃
-Temperature Min.(ts)	60∼180 seconds
Ts _{max} to T _L	
-Ramp-up Rate	3℃/second max.
Time maintained above:	
- Temperature(T _L)	217℃
-Time(T _L)	60∼150 seconds
Peak temperature(Tp)	245℃+0/-5℃
Time within 5°C of actual Peak temperature (tp)	6 seconds max.
Ramp-down Rate	6℃/second max.
Time 25℃ to Peak Temperature	8 minutes max.

Reliability Testing


Type of Test	Test Specifications	
	The part shall be capable of withstanding a storage	
High Temperature Test	temperature is +120°C for 120 hours	
	The part shall be capable of withstanding a storage	
Low Temperature Test	temperature is -40°C for120 hours	
Humidity Test	40±2°C, 90∼95% RH, 120 hours	
	Total 5 cycles,	
	1 cycle consists of:	
	-40 \pm 2°C, 30 minutes	
	$20\pm5^{\circ}$ C, 15 minutes	
	$120\pm2^{\circ}\text{C}$, 30 minutes	
Temperature Cycle Testing	20±5°C, 15 minutes	
	The part shall be subjected to a vibration cycle of	
	10 Hz for a period of 1 minute.	
	Total peak amplitude shall be 1.52mm (9.3g).	
	The vibration test shall consist of 2 hours per	
	plane in each three mutually perpendicular	
Vibration Test	planes for a total time of 6 hours.	
	Part shall be measured after applied shock	
	(980m/s ²) for each three mutually perpendicular	
Shock Test	directions to each of 3 times by half sine wave.	

² hours after the test the part shall meet specifications without any degradation in appearance and performance except SPL shall be $\pm 10 dB$ of the initial value.

Dimensions (Tolerance: ±0.5mm unless specified)




Suggested Land Pattern*




*This land pattern is advisory only and its use or adaptation is entirely voluntary. PUI Audio disclaims all liability of any kind associated with the use, application, or adaptation of this land pattern.

Packaging



Packaging Cont'd



NOTES:

- 1.1000PCS per box
- 2.Total 10 boxes per carton
- 3.Total 10000 PCS carton

This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

©2020, PUI Audio Inc.

Specifications Revisions

Revision	Description	Date
-	Released from Engineering	3/26/20

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- 2. Specifications subject to change or withdrawal without notice.