



Data Sheet AMM-3738-T

#### Features:

The AMM-3738-T analog MEMS microphone features a specialized preamplification ASIC that provides high sensitivity and high SNR output from a capacitive audio sensor. It's packaged for surface mounting and high temperature reflow assembly.

- -38dB sensitivity
- 65dB Signal-to-Noise
- Analog output
- Small 3.76mm x 2.95mm surface-mount package

#### **Specifications** ( $V_{DD} = 2.0V$ , $T_A = 23\pm2^{\circ}C$ , RH = $55\pm10\%$ , unless otherwise specified.)

Parameter	Test Condition	Value	Unit
Sensitivity	94dBSPL f <sub>IN</sub> = 1 kHz	-39 (min) -38 (typ) -37 (max)	dB
Supply Voltage		2.0 (typ)	$V_{DD}$
Supply Voltage Range		1.6 (min) 3.6 (max)	$V_{DD}$
Output Impedance	$f_{TEST} = 1kHz$	300 (max)	Ω
Supply Current	$1.6V \le V_{DD} \le 3.6V$	200 (max)	μA
Signal-to-Noise Ratio	f <sub>IN</sub> = 1kHz 94dBSPL A-weighted	65 (typ)	dB
Frequency Range	See Frequency Response Curve for response limits	20 – 20k	Hz
Total Harmonic Distortion	f <sub>IN</sub> = 1 kHz 94dBSPL	0.5 (max)	%
Acoustic Overload Point (AOP)	(f <sub>TEST</sub> = 1kHz, 10% THD) 124 (typ)		dB
Power Supply Rejection	100mV <sub>PP</sub> 217 Hz square wave on V <sub>DD</sub> , A-weighted	-98 (typ)	dB

# **Physical Properties**


Parameter	Condition	Value	Unit	
Directivity		Omnidirectional		
Weight		0.3 (max)	Grams	
Operating Temperature		-40 (min) 85 (max)	°C	
Storage Temperature		-40 (min) 100 (max)	°C	
MSL (Moisture Sensitivity Level)*		Class 1		
Acceptable Soldering Methods		See below for reflow soldering information		
Environmental Compliances		RoHS/Halogen Free		

<sup>\*</sup>MSL level dependent on product remaining in sealed packaging until use


**Absolute Maximum Ratings** 

Parameter	Condition	Value	Unit		
Supply Voltage		3.6 (max)	$V_{DC}$		
		-0.3 (min)			
Voltage on any Pin		V <sub>DD</sub> + 0.3	V		
		(max)			
Sound Pressure Level		160	dB		
Mechanical Shock		10000	G		
Vibration		Pre-MIL-STD-88	Pre-MIL-STD-883 Method		
VIDIGITOTI		2007, Test Co	2007, Test Condition B		


#### **Measurement Method**




#### **Measurement Circuit**




# Typical Frequency Response (Normalized to 0dB at 1kHz)




# Typical THD Vs SPL




# Typical THD Vs Frequency




# **Current Consumption Vs Voltage**




# **Typical Noise Floor**



## Typical PSRR Vs Frequency




## Typical Free Field Ultrasonic Response



#### Recommended Reflow Soldering Procedure (Recommended profile,

temperature ≤ 260°C, 30s maximum at peak temperature)



Important notes to minimize device damage

- 1. Do not handle the microphone with pick-and-place vacuum tools that could contact the microphone acoustic port hole.
- 2. Never expose the microphone's acoustic port hole to vacuum. Such exposure can damage or destroy the MEMS element.
- Never allow air to blow air into the microphone acoustic port hole. The port hole must be sealed to prevent particle contamination if a blown air-cleaning process is used,
- 4. A clean room environment is recommended for PCB assembly to avoid microphone contamination.
- 5. Do not use blown air or ultrasonic cleaning procedures on MEMS Microphones. A no-clean paste is recommended for the assembly, avoiding subsequent cleaning steps. cleaning substances can severely damage the microphone MEMS element.
- 6. it is recommended to cover the sound port with protective tape during PCB sawing or system assembly. This prevents blocking or partially blocking the acoustic port hole during PCB assembly.
- 7. Do not use excessive force to place the microphone on the PCB. Use industry standard pick and place tools to limit the mechanical force exerted on the package.

**Reliability Testing** (Samples under test are acclimated at  $T_A = 23\pm2^{\circ}$ C, R.H. =  $55\pm10\%$  for two hours. After each test completes and corresponding recovery time (if applicable) elapses, any measured sensitivity change is  $\leq \pm 3$ dB, unless otherwise specified.)


Type of Test	Test Specifications		
High Temperature Storage	1000hrs at 105±3°C		
Test	Two-hour recovery		
III I T	1000hrs at 105±3°C		
High Temperature	$V_{DD} = V_{DD}$ (max)		
Operational Test	Four-hour recovery		
Low Temperature Storage	1000hrs at -40±3°C		
Test	Two-hour recovery		
Lav. Tanana avatura	1000hrs at -40±3°C		
Low Temperature	$V_{DD} = V_{DD}$ (max)		
Operational Test	Four-hour recovery		
Lieb II. seciality Lieb	1000hrs at 85±3°C and 85%RH		
High Humidity, High	$V_{DD} = V_{DD}$ (max)		
Temperature Operating	Twelve-hour recovery		
Test	No corrosion or defamation inside the microphone		
I ti ada I ti waa i alifa a I ti ada	168hrs at 65±3°C and 95%RH		
High Humidity, High	$V_{DD} = V_{DD}$ (max)		
Temperature Operating	Twelve-hour recovery		
Test	No corrosion or defamation inside the microphone		
	Double-case method:		
To read a wash was Covalle	15min at -40±3°C		
Temperature-Cycle	Followed by		
Testing	15min at 125±3°C		
	100 cycles, two-hour recovery		
	Twelve minutes along the x, y, and z axis		
	$f_{IN} = 20$ Hz to 2kHz		
Vibration Test	20G peak acceleration		
	Two-hour recovery		
	Less than 1dB sensitivity change		
	Height: 1.5m		
	Fixture weight: 150±10g		
Shock Test	Fixture's sound hole diameter is ≥0.8mm		
SHOCK Test	Reference surface is marble floor		
	Duration: four corners x four times; six faces x four times		
	Less than 1dB sensitivity change		
Tumble Test	Height: 1.0m		
	Fixture weight: 150±10g		
	Fixture's sound hole diameter is ≥0.8mm		
	Duration: 300 cycles		
	Less than 1dB sensitivity change		
ESD Sensitivity	Measured according to MIL-STD-883G, Method 3015.7, Human		
	Body Model (HBM)		
	Identify ESD threshold levels indicating 3000V HBM passage.		

This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

© 2023, PUI Audio Inc.

Air Pressure Test	Air pressure = 0.3MPa Distance = 3cm
	Time = 10sec
	Air discharge port diameter exceeds microphone's acoustic port
	diameter
Structure Shock Test	10000G
	Pulse width = 0.1ms
	X, Y, and Z axis
	Three times along each axis
	Sensitivity changes less than 1dB

# **Dimensions** (Dimension are in mm.)



Item	Dimension	Tolerance(+/-)	Units
Length(L)	3.76	0.10	mm
Width(W)	2.95	0.10	mm
Height(H)	1.10	0.10	mm
Acoustic Port(AP)	Ø0.25	0.05	mm


Pin #	Pin Name	Туре	Description
1	Output	Signal	Output Signal
2	GND	Ground	Ground
3	GND	Ground	Ground
4	V <sub>DD</sub>	Power	Power Supply

Notes:

All dimensions are in millimeter (mm).


Tolerance±0.15mm unless otherwise specified.

### **Suggested Land Pattern\***




<sup>\*</sup>This land pattern is advisory only and its use or adaptation is entirely voluntary. PUI Audio disclaims all liability of any kind associated with the use, application, or adaptation of this land pattern.

### **Packaging**



All Dimensions are in millimeter (mm).



#### **Specifications Revisions**

Revision	Description	Date
Α	Released from Engineering	05-8-2023

#### Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are  $\pm 0.5$ mm and angles are  $\pm 3^{\circ}$ .
- 2. Specifications subject to change or withdrawal without notice.
- 3. This part is ROHS 2015/863/EU compliant.