



Base station

SICK
Sensor Intelligence.



Ordering information

Type	Part no.
Base station	6080756

Other models and accessories → www.sick.com/

Detailed technical data

Technical specifications

Accessory group	Rechargeable batteries and battery chargers
Accessory family	Base stations
Description	Wireless base station, supply voltage 5 V DC, current consumption max. 750 mA, interface: RS-232 True, USB
Enclosure rating	IP40
Dimensions (W x H x L)	105 mm x 80 mm x 140 mm
Housing color	Gray

Classifications

eCl@ss 5.0	27050604
eCl@ss 5.1.4	27050604
eCl@ss 6.0	27050604
eCl@ss 6.2	27050604
eCl@ss 7.0	27050604
eCl@ss 8.0	27050604
eCl@ss 8.1	27050604
eCl@ss 9.0	27050604
eCl@ss 10.0	27050604
eCl@ss 11.0	27050604
eCl@ss 12.0	27280105
ETIM 5.0	EC000359
ETIM 6.0	EC000359
ETIM 7.0	EC000359
ETIM 8.0	EC000359
UNSPSC 16.0901	26111704

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com