

USB-C to VGA and HDMI Adapter - 2-in-1 - 4K 30Hz - Space Grey

Product ID: CDP2HDVGA



This USB-C to VGA and HDMI adapter offers a portable solution for connecting your USB Type-C laptop to a VGA or HDMI display. The multiport video adapter also works as a splitter, enabling you to simultaneously output an identical video signal to two separate monitors (1 x HDMI and 1 x VGA).

Avoid the hassle of carrying different adapters, with a 2-in-1 USB-C monitor adapter. With VGA, and HDMI outputs, you can conveniently connect your laptop to any HDMI or VGA-equipped display, using this multiport adapter.


The adapter features a durable aluminum enclosure and can withstand being carried in your travel bag.

The HDMI output on this USB-C video adapter supports UHD resolutions up to 4K 30Hz, while the VGA output supports HD resolutions up to 1920 x 1200.

The USB-C video adapter has a Space Gray housing and built-in USB-C cable designed to match your Space Gray MacBook or MacBook Pro. The adapter is compatible with USB-C DP Alt Mode devices.

CDP2HDVGA is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect to virtually any VGA or HDMI display while traveling
- Use as a video splitter to output an identical image to a VGA and HDMI monitor simultaneously splitting the image
- Output video to a secondary VGA, or HDMI monitor

Features

- **USB C AV MULTIPORT ADAPTER:** Maximize your laptop's video compatibility with a 2-in-1 adapter that supports USBC to HDMI (digital) and VGA (analog)
- **DIGITAL 4K30 VIDEO:** USB C monitor adapter supports resource-demanding applications with support for UHD resolutions up to 4K 30Hz on the HDMI port and HD resolutions up to 1080p60Hz on the VGA port
- **SPACE GRAY:** The adapter is a great accessory for any laptop with a color and design to match your Space Gray MacBook, MacBook Pro or iPhone 15 [Plus/Pro/Max] and up
- **PERFECT FOR TRAVEL:** The USB Type C adapter has a small footprint and lightweight design with a built-in 6-inch USB-C cable for ease of use and travel
- **COMPATIBILITY:** This USB-C to DisplayPort video converter requires no software/drivers & is backwards compatible with DisplayPort 1.2; Works with Windows, MacOS, Linux, iPadOS, iOS, Chrome OS, Android

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	USB-C
AV Output	HDMI - 1.4 VGA
Chipset ID	ITE - IT6222

Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Video Revision	HDMI 1.4
Maximum Analog Resolutions	1920 x 1200 @ 60Hz (VGA)
Maximum Digital Resolutions	3840 x 2160 @ 30Hz (HDMI)

Supported Resolutions Maximum HDMI output:3840 x 2160 @ 30Hz

Maximum VGA output: 1920 x 1200 @ 60Hz

<i>Lower resolutions and refresh rates may also be supported</i>

Audio Specifications HDMI - 7.1 Channel Audio

MTBF 1,576,016 hours

Connector(s)

Connector A 1 - USB-C (24 pin) DisplayPort Alt Mode

Connector B 1 - VGA (15 pin, High Density D-Sub)

1 - HDMI (19 pin)

Special Notes / Requirements

Note HDMI and VGA can output video at the same time. If both video outputs are connected, they'll display the same image at a maximum resolution of 1920x1200 @ 60Hz

Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling

Environmental

Operating Temperature 0C to 45C (32F to 113F)

Storage Temperature -10C to 70C (14F to 158F)

Humidity 5~90% RH

Physical Characteristics

Color Space Gray

Accent Color Black

Material Aluminum

Cable Length 6.0 in [152.4 mm]

Product Length 8.1 in [205.0 mm]

Product Width	2.4 in [6.2 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	1.5 oz [43.0 g]

Packaging Information

Package Quantity	1
Package Length	5.9 in [15.0 cm]
Package Width	3.2 in [8.2 cm]
Package Height	0.8 in [20.0 mm]
Shipping (Package) Weight	2.1 oz [60.0 g]

What's in the Box

Included in Package	1 - Travel A/V Adapter
---------------------	------------------------

**Product appearance and specifications are subject to change without notice.*