



## Main

|                               |                  |
|-------------------------------|------------------|
| Range of Product              | L100/300         |
| Series name                   | Severe duty mill |
| Product or Component Type     | Limit switch     |
| Product Specific Application  | Mill switch      |
| Device short name             | L100[RETURN]L300 |
| Body type                     | Fixed            |
| Head type                     | Rotary head      |
| Sale per indivisible quantity | 1                |

## Complementary

|  |   |
|--|---|
| Base plate style                             | Style 2   |
| Body material                                | Cast aluminium  |
| Fixing Mode                                  | By the body   |
| Type of operator                             | spring return without operating lever   |
| Contact sequence number                      | 13  |
| Function Available                           | -   |
| Switch actuation                             | CCW<br>From right   |
| Type of approach                             | Lateral approach  |
| Electrical connection                        | Screw-clamp terminals AWG 22...AWG 12   |
| Cable entry                                  | 1 entry for 3/4" - 14 NPT ANSI B1.20.1  |
| Number of poles                              | 3   |
| CW operation contacts                        | 1 NC + 2 NO   |
| CCW operation contacts                       | 2 NC + 1 NO   |
| Contacts style                               | A   |
| Switch Function                              | TPDT-DB   |
| Contact form                                 | Form XXY  |
| Contacts material                            | 90/10 AgCdO on copper backing stationary contact<br>Silver on steel backing moveable contact  |
| Contacts usage                               | -   |
| Contact operation                            | Snap action   |
| Positive opening                             | Without   |
| Minimum torque for tripping                  | 190 ozf.in  |
| Maximum actuation speed                      | 90 Ft/Min with 45° cam angle, levers only<br>130 ft/min with 30° cam angle, levers only   |
| Tripping angle                               | 17 °  |
| Maximum displacement angle                   | 80 °  |
| Repeat accuracy                              | +/- 0.03 %  |
| Contact code designation                     | A600, AC (Ue = 600 V) Ie = 5 A NEMA rating designation<br>A600, AC (Ue = 480 V) Ie = 6.25 A NEMA rating designation<br>A600, AC (Ue = 240 V) Ie = 12.5 A NEMA rating designation<br>A600, AC (Ue = 120 V) Ie = 20 A NEMA rating designation<br>P600, DC (Ue = 600 V) Ie = 0.2 A NEMA rating designation<br>P600, DC (Ue = 250 V) Ie = 1 A NEMA rating designation<br>P600, DC (Ue = 120 V) Ie = 5 A NEMA rating designation |
| [Ithe] conventional enclosed thermal current | 20 A  |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TWSS Holding nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|  |   |
|--|---|
| [Ui] rated insulation voltage          | 600 V 3)IEC 60947-1<br>600 V 3)UL 508<br>600 V 3)CSA C22.2 No 14                      |
| [Uimp] rated impulse withstand voltage | 2.5 KV AC for 1 minute CE<br>2.2 KV AC for 1 minute UL<br>2.64 kV AC for 1 minute CSA |
| Short-circuit protection               | 20 A Bussmann class CC KTK-R-20 non-time delay  |
| Width                                  | 2.25 in (57.15 mm)  |
| Height                                 | 4.95 in (125.73 mm)   |
| Depth                                  | 3.41 in (86.61 mm)  |
| Net Weight                             | 1.5 lb(US) (0.68 kg)  |
| Terminals description ISO n°1          | (5-6) center contact<br>(1-2) left side contact<br>(3-4) right side contact           |

## Environment

|                                       |  |
|---------------------------------------|--|
| Shock resistance                      | 30 gn 9 ms IEC 60068-2-27  |
| Vibration resistance                  | 10 gn 10...55 Hz)IEC 60068-2-6   |
| NEMA degree of protection             | NEMA 1 Nema type 250<br>NEMA 2 Nema type 250<br>NEMA 4 Nema type 250<br>NEMA 12 Nema type 250<br>NEMA 13 Nema type 250 |
| IP degree of protection               | IP67 conforming to IEC 60529   |
| Electrical shock protection class     | Class 0 IEC 61140  |
| Ambient air temperature for operation | -10...185 °F (-23...85 °C)   |
| Ambient Air Temperature for Storage   | -10...185 °F (-23...85 °C)   |
| Protective treatment                  | Corrosion resistant gray paint   |

## Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10DS122426 |
| Discount Schedule | 0DS1         |
| GTIN              | 785901162988 |
| Returnability     | No           |
| Country of origin | MX           |

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 12.70 in (32.258 cm) |
| Package 1 Width              | 5.00 in (12.7 cm)    |
| Package 1 Length             | 32.26 in (81.935 cm) |
| Package 1 Weight             | 24.00 oz (680.389 g) |

## Offer Sustainability

|  |   |
|--|---|
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| Environmental Disclosure                   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile                        | No need of specific recycling operations  |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|