



# GSE2FS-E1151

G2

MINIATURE PHOTOELECTRIC SENSORS

**SICK**  
Sensor Intelligence.



### Ordering information

| Type         | Part no. |
|--------------|----------|
| GSE2FS-E1151 | 1095471  |

Other models and accessories → [www.sick.com/G2](http://www.sick.com/G2)

Illustration may differ



### Detailed technical data

#### Features

|  |                                   |
|--|-----------------------------------|
| <b>Functional principle</b>            | Through-beam photoelectric sensor |
| <b>Dimensions (W x H x D)</b>          | 4.5 mm x 21 mm x 11 mm            |
| <b>Housing design (light emission)</b> | Rectangular                       |
| <b>Minimum detectable object (MDO)</b> | 1 mm                              |
| <b>Sensing range max.</b>              | 0 mm ... 700 mm                   |
| <b>Sensing range</b>                   | 0 mm ... 500 mm                   |
| <b>Type of light</b>                   | Visible red light                 |
| <b>Light source</b>                    | PinPoint LED <sup>1)</sup>        |
| <b>Light spot size (distance)</b>      | Ø 60 mm (500 mm)                  |
| <b>Wave length</b>                     | 660 nm                            |
| <b>Adjustment</b>                      | None                              |

<sup>1)</sup> Average service life: 100,000 h at T<sub>J</sub> = +25 °C.

#### Mechanics/electronics

|                                     |                                   |
|-------------------------------------|-----------------------------------|
| <b>Supply voltage U<sub>B</sub></b> | 10 V DC ... 30 V DC               |
| <b>Ripple</b>                       | < 5 V <sub>pp</sub> <sup>1)</sup> |
| <b>Current consumption</b>          | 20 mA <sup>2)</sup>               |

<sup>1)</sup> May not exceed or fall below U<sub>v</sub> tolerances.

<sup>2)</sup> Without load.

<sup>3)</sup> Signal transit time with resistive load.

<sup>4)</sup> With light/dark ratio 1:1.

<sup>5)</sup> Do not bend below 0 °C.

<sup>6)</sup> A = V<sub>S</sub> connections reverse-polarity protected.

<sup>7)</sup> C = interference suppression.

<sup>8)</sup> D = outputs overcurrent and short-circuit protected.

|  |   |
|--|---|
| <b>Switching output</b>                              | NPN   |
| <b>Switching mode</b>                                | Dark switching  |
| <b>Output current <math>I_{\max}</math></b>          | $\leq 50$ mA  |
| <b>Response time</b>                                 | $< 0.625$ ms <sup>3)</sup>                            |
| <b>Switching frequency</b>                           | 800 Hz <sup>4)</sup>                                  |
| <b>Connection type</b>                               | Cable, 3-wire, 2 m <sup>5)</sup>                      |
| <b>Cable material</b>                                | PVC   |
| <b>Cable diameter</b>                                | $\varnothing 2.3$ mm                                  |
| <b>Circuit protection</b>                            | A <sup>6)</sup><br>C <sup>7)</sup><br>D <sup>8)</sup> |
| <b>Weight</b>  | 40 g  |
| <b>Housing material</b>                              | Plastic, VISTAL®                                      |
| <b>Optics material</b>                               | Plastic, MABS   |
| <b>Enclosure rating</b>                              | IP67  |
| <b>Ambient operating temperature</b>                 | -20 °C ... +50 °C                                     |
| <b>Ambient temperature, storage</b>                  | -40 °C ... +70 °C                                     |
| <b>UL File No.</b>                                   | NRKH.E348498 & NRKH7.E348498                          |
| <b>Repeatability (<math>T_a</math> not constant)</b> | 0.1 mm  |

1) May not exceed or fall below  $U_V$  tolerances.

2) Without load.

3) Signal transit time with resistive load.

4) With light/dark ratio 1:1.

5) Do not bend below 0 °C.

6) A =  $V_S$  connections reverse-polarity protected.

7) C = interference suppression.

8) D = outputs overcurrent and short-circuit protected.

## Classifications


|                     |          |
|---------------------|----------|
| <b>eCl@ss 5.0</b>   | 27270901 |
| <b>eCl@ss 5.1.4</b> | 27270901 |
| <b>eCl@ss 6.0</b>   | 27270901 |
| <b>eCl@ss 6.2</b>   | 27270901 |
| <b>eCl@ss 7.0</b>   | 27270901 |
| <b>eCl@ss 8.0</b>   | 27270901 |
| <b>eCl@ss 8.1</b>   | 27270901 |
| <b>eCl@ss 9.0</b>   | 27270901 |
| <b>eCl@ss 10.0</b>  | 27270901 |
| <b>eCl@ss 11.0</b>  | 27270901 |
| <b>eCl@ss 12.0</b>  | 27270901 |
| <b>ETIM 5.0</b>     | EC002716 |
| <b>ETIM 6.0</b>     | EC002716 |
| <b>ETIM 7.0</b>     | EC002716 |
| <b>ETIM 8.0</b>     | EC002716 |

UNSPSC 16.0901

39121528


**Connection diagram**

Cd-049



**Characteristic curve**


Operating reserve



① GSE2 Flat, GSE2 Flat Side, 500 mm


### Light spot size

GSE2 Flat Side, 500 mm




### Sensing range diagram

GSE2 Flat, GSE2 Flat Side, 500 mm





### Dimensional drawing (Dimensions in mm (inch))



- ① Optical axis, receiver
- ② Optical axis, sender

### Recommended accessories

Other models and accessories → [www.sick.com/G2](http://www.sick.com/G2)

|   | Brief description  | Type                   | Part no. |
|---|--|------------------------|----------|
| Mounting brackets and plates  |  |                        |          |
|  | 10 pieces, Mounting plate for direct mounting, from the rear, on wall or machine, not adjustable. 10 Piece,Black ,Plastic, VISTAL®. Suitable for GSE2FS only | BEF-G2F-SIDE-SPACER-M2 | 2107264  |
| Plug connectors and cables  |  |                        |          |
|  | Head A: male connector, M8, 3-pin, straight<br>Cable: unshielded   | STE-0803-G             | 6037322  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)