

Actuator

46-
2231.31H0.000

Distribution by
Newark



<https://newark.eao.com/p/46-2231.31H0.000>

Your product:



46-2231.31H0.000 Actuator

FRONT

Front form:	round
Front dimension:	Ø 29,5 mm
Front bezel material:	Metal
Front bezel colour:	Silver

MOUNTING

Design:	raised
Mounting cut-out:	Ø 22.3 mm

OPERATING-/INDICATION PART

Lens illumination:	illuminative
Lens material:	Plastic
Lens optics:	transparent
Lens colour:	Green
Lens shape:	flush

ELECTRICAL CHARACTERISTICS

Protection class:	II
--------------------------	----

MECHANICAL CHARACTERISTIC

Weight:	0.033 kg
Mechanical lifetime:	1 Mio. cycles of operation

Switching action: Momentary
Tightening torque: 2 ... 3 Nm (17.7 ... 26.6 Lb-in)

AMBIENT CONDITION

Operating temperature: - 25 °C ... + 55 °C
Shock resistance: 30g, 18ms (EN-IEC 60068-2-27)
50g, 11ms (EN-IEC 60068-2-27)
Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
IP front protection: IP65
IK front protection: IK03
Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

CERTIFICATE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508
Conformities: CE

OTHER

max. number of switching elements: 6
Housing colour: Black
Housing material: Plastic
Short Description: Actuator, Ø 22.3 mm, Ø 29,5 mm, flush, illuminative, Green, Plastic, transparent, round, Silver, Metal, Momentary, IP65, IK03

Dimension drawings:

