

Actuator

46-
2828.3CV0.001

Distribution by
Newark



<https://newark.eao.com/p/46-2828.3CV0.001>

Your product:



46-2828.3CV0.001 Actuator

FRONT

Front bezel material:	Metal
Front dimension:	Ø 30 mm
Front bezel colour:	Silver
Front form:	round

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

OPERATING-/INDICATION PART

Lever material:	plastic
Lever colour:	Black
Lever shape:	short
Lever bar colour:	White

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Switching angle:	90°
Mechanical lifetime:	1 Mio. cycles of operation
Weight:	0.038 kg

Tightening torque: 2 ... 3 Nm (17.7 ... 26.6 Lb-in)

Switching action: Maintained - Maintained

Switching positions: 2 positions

AMBIENT CONDITION

Operating temperature: - 25 °C ... + 55 °C

IP front protection: IP65

Shock resistance: 30g, 18ms (EN-IEC 60068-2-27)
50g, 11ms (EN-IEC 60068-2-27)

IK front protection: IK03

Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

CERTIFICATE

Conformities: CE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER


Housing colour: Black

max. number of switching elements: 4

Housing material: Plastic

Short Description: Actuator, Ø 22.3 mm, Ø 30 mm, non illuminative, Black, short, round, Silver, Metal, Maintained - Maintained, IP65, IK03

Switching positions:



Dimension drawings:

