

Actuator

46-
2925.1000.7P8

Distribution by
Newark



<https://newark.eao.com/p/46-2925.1000.7P8>

Your product:



46-2925.1000.7P8 Actuator

FRONT

Front dimension:	Ø 29 mm
Front bezel colour:	Black
Front bezel material:	Plastic
Front form:	round

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

ELECTRICAL CHARACTERISTICS

Protection class:	II
--------------------------	----

MECHANICAL CHARACTERISTIC

Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Weight:	0.076 kg
Switching action:	Rest - Maintained (a)
Mechanical lifetime:	50 000 cycles of operation
Switching positions:	2 positions
Switching angle:	60° right

AMBIENT CONDITION

Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
--------------------------	--

Operating temperature: - 25 °C ... + 55 °C

IK front protection: IK06

Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

IP front protection: IP65

Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

CERTIFICATE

Conformities: CE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

Approbations: CSA, EAC, UL

OTHER


max. number of switching elements: 8

Short Description: Actuator, Ø 22.3 mm, Ø 29 mm, round, Black, Plastic, Rest - Maintained (a), IP65, IK06


Housing material: Plastic

Housing colour: Black

Switching positions:



Mounting cut-outs:



Dimension drawings:

