

Actuator

46-
2134.3120.000

Distribution by
Newark



<https://newark.eao.com/p/46-2134.3120.000>

Your product:



46-2134.3120.000 Actuator

FRONT

Front bezel material:	Metal
Front form:	round
Front dimension:	Ø 29,5 mm
Front bezel colour:	Silver

MOUNTING

Design:	raised
Mounting cut-out:	Ø 22.3 mm

OPERATING-/INDICATION PART

Lens material:	Plastic
Lens colour:	Red
Lens shape:	flush
Lens illumination:	non illuminative
Lens optics:	opaque

ELECTRICAL CHARACTERISTICS

Protection class:	II
--------------------------	----

MECHANICAL CHARACTERISTIC

Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Switching action:	Maintained

Mechanical lifetime: 500 000 cycles of operation

Weight: 0.033 kg

AMBIENT CONDITION

Operating temperature: - 25 °C ... + 55 °C

Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

IK front protection: IK03

IP front protection: IP65

Shock resistance: 50g, 11ms (EN-IEC 60068-2-27)

CERTIFICATE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

Conformities: CE

OTHER

Housing colour: Black

Short Description: Actuator, Ø 22.3 mm, Ø 29,5 mm, flush, non illuminative, Red, Plastic, opaque, round, Silver, Metal, Maintained, IP65, IK03

Housing material: Plastic

max. number of switching elements: 6

Dimension drawings:

