

WL9-3N1102S07

W9

**SMALL PHOTOELECTRIC SENSORS** 





# Ordering information

Туре	Part no.
WL9-3N1102S07	1076074

Other models and accessories → www.sick.com/W9

Illustration may differ



#### Detailed technical data

#### **Features**

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Autocollimation
Dimensions (W x H x D)	12.2 mm x 50 mm x 23.6 mm
Housing design (light emission)	Rectangular
Mounting hole	МЗ
Sensing range max.	0 mm 290 mm <sup>1)</sup>
Sensing range	0 mm 125 mm <sup>1)</sup>
Type of light	Visible red light
Light source	PinPoint LED <sup>2)</sup>
Light spot size (distance)	Ø 3 mm (35 mm)
Wave length	650 nm
Adjustment	Single teach-in button
Special feature	Front screen printing for a small light spot
Special applications	Detecting small objects

<sup>1)</sup> Reflective tape REF-IRF-56.

 $<sup>^{2)}</sup>$  Average service life: 100,000 h at  $T_{U}$  = +25 °C.

#### Mechanics/electronics

Supply voltage $\mathbf{U}_{\mathrm{B}}$	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	30 mA <sup>3)</sup>
Switching output	NPN <sup>4)</sup>
Output function	Complementary
Switching mode	Light/dark switching <sup>4)</sup>
Output current I <sub>max.</sub>	$\leq$ 100 mA $^{5)}$
Response time	< 0.5 ms <sup>6)</sup>
Switching frequency	1,000 Hz <sup>7)</sup>
Connection type	Cable, 4-wire, 2 m <sup>8)</sup>
Cable material	PVC
Conductor cross section	0.14 mm <sup>2</sup>
Circuit protection	A <sup>9)</sup> B <sup>10)</sup> C <sup>11)</sup>
Protection class	III
Weight	80 g
Polarisation filter	✓
Housing material	Plastic, VISTAL®
Optics material	Plastic, PMMA
Enclosure rating	IP66 IP67 IP69K
Special feature	Front screen printing for a small light spot
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

#### Classifications

ECLASS 5.0	27270902
ECLASS 5.1.4	27270902
ECLASS 6.0	27270902
ECLASS 6.2	27270902

 $<sup>^{2)}</sup>$  May not exceed or fall below  $\mathrm{U}_{\mathrm{V}}$  tolerances.

<sup>3)</sup> Without load.

 $<sup>^{4)}</sup>$  Q = light switching.

 $<sup>^{5)}</sup>$  At and above Tu 50 °C, a max. load current of Imax. = 50 mA is permitted.

<sup>&</sup>lt;sup>6)</sup> Signal transit time with resistive load.

<sup>7)</sup> With light/dark ratio 1:1.

<sup>8)</sup> Do not bend below 0 °C.

 $<sup>^{9)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

<sup>&</sup>lt;sup>10)</sup> B = inputs and output reverse-polarity protected.

 $<sup>^{11)}</sup>$  C = interference suppression.


# WL9-3N1102S07 | W9

# SMALL PHOTOELECTRIC SENSORS

ECLASS 7.0	27270902
ECLASS 8.0	27270902
ECLASS 8.1	27270902
ECLASS 9.0	27270902
ECLASS 10.0	27270902
ECLASS 11.0	27270902
ECLASS 12.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528


# Adjustments

Single teach-in button



- $\ensuremath{\mathfrak{G}}$  LED indicator yellow: Status of received light beam
- 4 LED indicator green: power on
- ® Teach-in button

# Connection type



#### Connection diagram


Cd-094



#### Characteristic curve

WL9-3, red light, 290 mm


Function reserve



① Reflective tape REF-IRF-56


### Light spot size

WL9-3, red light, 0.4 m



#### Sensing range diagram


WL9-3, red light, 0.4 m



- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflective tape REF-IRF-56

#### Dimensional drawing (Dimensions in mm (inch))

WL9-3, WSE9-3



- ① Sender and receiver optical axis center
- ② Mounting hole M3 (Ø 3.1 mm)
- $\ensuremath{\mathfrak{G}}$  LED indicator yellow: Status of received light beam
- ④ LED indicator green: power on
- ⑤ Connecting cable or connector
- Male connector M8, 4-pin
- 7 Male connector M12, 4-pin

#### Recommended accessories

Other models and accessories → www.sick.com/W9

	Brief description	Туре	Part no.
Mounting brackets and plates			
7	Mounting bracket, steel, zinc coated, mounting hardware included	BEF-WN-W9-2	2022855
Plug connectors and cables			
The state of the s	Head A: male connector, M12, 4-pin, straight Cable: unshielded	STE-1204-G	6009932

	Brief description	Туре	Part no.
Reflectors			
	Rectangular, screw connection, 40 mm x 60 mm, PMMA/ABS, Screw-on, 2 hole mounting	PL40A	1012720

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

