53C3200K Page 1



→ Honeywell.com → Automation & Control Solutions

Distributor Inventory 2

Honeywell Sensing and Control





narrow your search

Products

Search

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7074)
- Switches (9814)

Technology

- Control and
- Instrumentation (1063)

 Electromechanical
- (9357)
- Microstructure (2328)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...



53C3200K Conductive Plastic Potentiometers

Documentation

53 Series Industrial Potentiometer, Conductive Plastic Element, Solder lug Terminals, 2 W Power Rating, 200 kOhm Resistance Value

Sales & Service 2

Application Notes



(Home: Products)

Actual product appearance may vary.

Overview

Need Help?

Click here to contact us 3



Potentiometer Type Industrial

Specs

Element Type Conductive Plastic

Terminal Solder lug
Power Rating 2 W
Resistance Value 200 kOhm
Resistance Tolerance ± 10 %

Linearity ± 5 %

Bushing Thread 9,53 mm [0.375 in] x 32 NEF-2A

Bushing Length 9,53 mm [0.375 in]

 Bushing Type
 Standard

 Shaft Diameter
 6,35 mm [0.25 in]

 Shaft Length
 22,23 mm [0.875 in]

Shaft Ending Slotted

Body 27.8 mm [1.094 in] diameter max. except at terminal standoff

Electrical Taper Linear

Operating Temperature $\,$ -55 °C to 120 °C [-67 °F to 248 °F]

Working Voltage (Max.) 500 V
Rotational Life 25000 cycles
Mechanical Rotation 312°
Availability Global
Series Name 53

UNSPSC Code 4111363300

UNSPSC Commodity 4111363300 Potentiometers

Terms & Conditions | Privacy Statement | Site Map