




HONEYWELL PART NUMBER
141SM32-H2
PRODUCT CODE TYS0299

REV	DOCUMENT	CHANGED BY	CHECK
3	0041782	PK 21JUL08	ASD



- NOTES
- $\triangle 1$  MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF  $\phi .087$  MAX ON  $.375 \pm .002$  CENTERS
  - 2 - TERMINALS ARE PLATED FOR SOLDERING
  - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF  $250^{\circ}F$
  - $\triangle 4$  - CHARACTERISTICS TAKEN AT POINT "A"
  - $\triangle 5$  - CUSTOMER'S TARGET DIFF TRAVEL RANGE AT POINT A ON LEAF IS 0.0065-0.0100
  - 6 - CORRESPONDS TO NASON PART NUMBER SM-1773

RELEASE NO.	PR - 22437
REPLACES	-

CHARACTERISTICS $\triangle 4$
OPERATING FORCE - - - -12 OZ MAX
RELEASE FORCE - - - - 2 OZ MIN
DIFFERENTIAL TRAVEL $\triangle 5$ - .005 MIN
OVERTRAVEL - - - - .011 MIN

ELECTRICAL DATA	
CONTACT ARRANGEMENT SPDT	
APPROVALS	KEMA, CE 11A 250V ~ T85 1E4 5A 30 Vdc T85 1E4
	UL, CSA 11A 1/4 HP 125 250 VAC 5A 30 VDC   BRAND L190

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X $\pm$
ONE PLACE .X $\pm$
TWO PLACE .XX $\pm$
THREE PLACE .XXX $\pm$
FOUR PLACE .XXXX $\pm$
ANGLES $\pm$
0.030
0.015
0.005
-
THIRD ANGLE PROJECTION

DRAWN	VK	30 OCT 07
CHECK	RJ	30 OCT 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

<b>Honeywell</b>			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
<b>B</b>	<b>I</b>	<b>141SM32-H2</b>	<b>3</b>
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1