


HONEYWELL
PART NUMBER
V7-4A33E9-000-2

REV	DOCUMENT	CHANGED BY	CHECK
A	0038443	SS 25MAR08	BLR

PRODUCT CODE: CWC3910
SUPERSEDES: X201252-V7



NOTES:

- 1 - SWITCH MATERIALS WILL WITHSTAND 150°C
- 2 - RAW MATERIAL - COMMERCIAL STANDARD

CHARACTERISTICS	
OPERATING FORCE----	25 GRAMS MAX
DIFFERENTIAL TRAVEL----	.002-.010
OVERTRAVEL-----	.050 MIN
FREE POSITION-----	.625 MAX
RELEASE TRAVEL-----	.010 MIN

ELECTRICAL DATA	
CONTACT ARRANGEMENT S P N C	
L162	
5A 125, 250, 277 VAC 1/10HP 250 VAC	

DESIGN UNITS: INCH			
TOLERANCES UNLESS NOTED:			
NO PLACES	X	±	.040
ONE PLACE	.X	±	.030
TWO PLACE	.XX	±	.015
THREE PLACE	.XXX	±	.005
ANGLES	X	±	-
THIRD ANGLE PROJECTION			

DRAWN	SS	25MAR08
CHECK	BLR	25MAR08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
Pro/ENGINEER		2D

Honeywell					
TITLE SWITCH, BASIC					
SIZE	TYPE	CAGE CODE	DRAWING NAME	REV	
B	I	-	V7-4A33E9-000-2	A	
SCALE	NTS	SHEET		1 OF 1	