



HONEYWELL

135-253LAG-J01

See full Datasheet below...

onlinecomponents.com

THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

BUY NOW



MASTERTM
ELECTRONICS

BUY NOW

masterelectronics.com & onlinecomponents.com
are **authorized** e-commerce distributors
of electronic components.



narrow your search

Products

- ? Controls and Monitoring (286)
- ? Machine Safety (865)
- ? Sensors (5925)
- ? Switches (9620)
- ? Wireless (45)

Technology

- ? Electromechanical(9137)
- ? Magnetic(540)
- ? Microstructure (1830)
- ? Platinum thin film(56)
- ? Thick Film(1372)
- ? More...

135-253LAG-J01

(Home: Products : Sensors » Temperature Sensors » Discrete Thermistors » 135)



Actual product appearance may vary.

135 Series, glass encapsulated chip DO -35 type, 25,000 Ohm resistance, ±10.0% tolerance, 25/85 BETA = 3974

[Sales & Service](#)

[Distributor Inventory](#)

Overview

Specs

Documentation

Application Notes

Description

135 Series Thermistors are high-quality, hermetically-sealed, glass-encapsulated units in an axial lead package. They cover the full temperature range of -60 °C to 300 °C [-76 °F to 572 °F]. The uniform dimensions are often suited for automated assembly. The tinned copperclad, steel leads are both solderable and weldable. These rugged sensors are designed for many applications which demand reliability at low cost. Available on tape and reel for automated assembly.

Features

Features

- ? Cost effective
- ? Rugged DQ35 glass encapsulation
- ? High temperature capability
- ? Available on tape and reel

Potential Applications

Potential Applications

- ? Consumer electronics
- ? PCB temperature sensing
- ? Communications
- ? Fire detection
- ? Computers
- ? Low -cost applications with a maximum temperature of 300 °C [615 °F]
- ? Automotive

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site WGLA and WPMM XYR6000™](#)

[find out more](#)

White Papers

Wireless Switches Offer Unlimited Benefit

Basic Switches Are Not Created Equal

Applying Precision Switches Sensors for Medical Devices

New Ways to Measure Torque

Choosing Safety Switches

Specifying Hour Meters

Need Help?

[Click here to contact us](#)

contacts

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

Meet Dr. Larry

VIDEO- Dr. Larry Goldstein explains our newest and best technologies.



[Meet Dr. Larry](#)

My Links

- [Login to iCOM](#)
- [Login to Rep/AD Portal](#)
- [Login to Digital University](#)

News Center

HONEYWELL INTRODUCES NEW HUMIDICON™ DIGITAL HUMIDITY/TEMPERATURE SENSORS

HONEYWELL EXPANDS INDUSTRYLEADING TRUSTABILITY® PLATFORM WITH NEW BOARD MOUNT ULTRA-LOW PRESSURE SENSORS

HONEYWELL INTRODUCES TRUSTABILITY® NSC SERIES, UNCOMPENSATED / UNAMPLIFIED BOARD MOUNT PRESSURE SENSORS



MICRO SWITCH Anniversary site