



Click [here](#) for the 3D model.

Dimensions

D	25mm +1mm
L	45mm +/-2mm
S	10mm +/-0.1mm
LL	4mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------

General Information

Series	ALA8A
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	3 Pin Short
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Typical Component Weight	40 g
Shelf Life	156 Weeks

Specifications

Capacitance	270 uF
Capacitance Tolerance	20%
Voltage DC	400 VDC, 440 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	5000 Hrs (Rated Voltage And Ripple Current At 105C)
ESR	568 mOhms (100Hz 20C)
Ripple Current	1.6 Amps (100Hz 105C), 4 Amps (10kHz 105C)
Leakage Current	324 uA (5min 20°C)