

Spezifikation für Freigabe / specification for release

Kunde / customer : _____

Artikelnummer / part number : **742863147**




Bezeichnung : **Multilayer-SMD-Ferrit WE-CBF HF (HighFrequency)**

description : **Multilayer-SMD-Ferrit WE-CBF HF (HighFrequency)**

DATUM / DATE : 2009-01-15

A Mechanische Abmessungen / dimensions:




| | | Größe / size 0603 | |
|---|-------------------|-------------------|--|
| A | 1.6 ± 0.15 | mm | |
| B | 0.8 ± 0.15 | mm | |
| C | 0.8 ± 0.15 | mm | |
| D | 0.3 ± 0.2 | mm | |
| | | | |
| | | | |
| | | | |

B Elektrische Eigenschaften / electrical properties:

| Eigenschaften / properties | Testbedingungen / test conditions | | Wert / value | Einheit / unit | tol. |
|--------------------------------|-----------------------------------|-----------------|--------------|----------------|-------------|
| Impedanz / impedance | 100 MHz | Z | 470 | Ω | ±25% |
| Min. Impedanz / min. impedance | 1 GHz | Z | 600 | Ω | min. |
| DC-Widerstand / DC-resistance | @ 20°C | R _{DC} | 0.32 | Ω | max. |
| Nennstrom / rated current | ΔT=20 K | I _{DC} | 500 | mA | max. |
| | | | | | |

C Lötpad / soldering spec.:



D Prüfgeräte / test equipment:

Agilent E4991A / Agilent 16197A für/for Z und/and material
GMC 271 für/for R_{DC}

E Testbedingungen / test conditions:

Luftfeuchtigkeit / humidity: 33%
 Umgebungstemperatur / ambient temp.: + 20°C

F Werkstoffe & Zulassungen / material & approvals:

Basismaterial / base material: Ferrit / ferrite

G Eigenschaften / general specifications:

.....
 Betriebstemp. / operating temperature: -55°C - +125°C

 Lagertemperatur der Rollen vor Verarbeitung /
 storage temperature of Tape & Reel bevor mounting:
 -20°C - + 60°C

| | | | | |
|-------------------------------------|--------------------------|------|-------------------------|--------------|
| Freigabe erteilt / general release: | Kunde / customer | | | |
| | | | | |
| Datum / date | Unterschrift / signature | | | |
| | Würth Elektronik | | | |
| | | | | |
| Geprüft / checked | Kontrolliert / approved | SMU | Version 1 | 09-01-15 |
| | | Name | Änderung / modification | Datum / date |

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
<http://www.we-online.com>

Spezifikation für Freigabe / specification for release

Kunde / customer : _____

Artikelnummer / part number : **742863147**




Bezeichnung : **Multilayer-SMD-Ferrit WE-CBF HF (HighFrequency)**

description : **Multilayer-SMD-Ferrit WE-CBF HF (HighFrequency)**

WÜRTH ELEKTRONIK

DATUM / DATE : 2009-01-15

H Impedanzverlauf / impedance curve:



| | | | | |
|-------------------------------------|--------------------------|------|-------------------------|--------------|
| Freigabe erteilt / general release: | Kunde / customer | | | |
| Datum / date | Unterschrift / signature | | | |
| | Würth Elektronik | | | |
| Geprüft / checked | Kontrolliert / approved | SMU | Version 1 | 09-01-15 |
| | | Name | Änderung / modification | Datum / date |

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
http://www.we-online.com

Spezifikation für Freigabe / specification for release

Kunde / customer : _____

Artikelnummer / part number : **742863147**



Bezeichnung : **Multilayer-SMD-Ferrit WE-CBF HF (HighFrequency)**

description : **Multilayer-SMD-Ferrit WE-CBF HF (HighFrequency)**

DATUM / DATE : 2009-01-15

I Rollenspezifikation / Tape & Reel specification :

Die Verpackung ist bezogen auf die internationale Norm IEC 60286 -3:2007

Packaging is referred to the international standard IEC 60286 -3:2007

| Bauform / size | Gurt Material / tape material | Bandbreite / band width | VPE | Teilenummer/ Part no. |
|----------------|-------------------------------|-------------------------|------|-----------------------|
| 0603 | paper | 8mm | 4000 | 742 86x xxx |

J Lötprofil / Solder specification :

Refer to the Würth Elektronik eiSos STANDARD REFLOW SOLDER PROFILE

| | | | | |
|-------------------------------------|--------------------------|------|-------------------------|--------------|
| Freigabe erteilt / general release: | Kunde / customer | | | |
| | | | | |
| Datum / date | Unterschrift / signature | | | |
| | Würth Elektronik | | | |
| Geprüft / checked | Kontrolliert / approved | Name | Änderung / modification | Datum / date |
| | | SMU | Version 1 | 09-01-15 |

This electronic component has been designed and developed for usage in general electronic equipment. Before incorporating this component into any equipment where higher safety and reliability is especially required or if there is the possibility of direct damage or injury to human body, for example in the range of aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc, Würth Elektronik eiSos GmbH must be informed before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400

<http://www.we-online.com>