



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:



PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.095 ohms ±10%
D.C. RESISTANCE	3-4 @20°C	0.115 ohms ±10%
D.C. RESISTANCE	5-7 @20°C	0.040 ohms ±10%
D.C. RESISTANCE	6-8 @20°C	0.057 ohms ±10%
INDUCTANCE	3-4 10kHz, 100mVAC, Ls	63.0uH ±10%
LEAKAGE INDUCTANCE	3-4 tie(1+2, 5+6+7+8), 100kHz, 50mVAC, Ls	600nH max.
DIELECTRIC RATING	1-8 tie(2+3, 5+6), 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(3-4):(5-7)	3:1, ±1%
URNS RATIO	(3-4):(8-6)	3:1, ±1%
URNS RATIO	(3-4):(2-1)	3:1, ±1%

TERM. NO.'s FOR REF. ONLY



DOT LOCATES TERM. #1

LOT CODE & DATE CODE



CUSTOMER TO DETERMINE LAND LAYOUT

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +85°C including temp rise.

REV.	DATE
6B	1/09
6A	9/08

Packaging Specifications  
 Method: Tape & Reel  
 PKG-0328  
 www.midcom-inc.com

Unless otherwise specified:  
 Tolerances: Fractions: ±1/64  
 Angles: ±1° Decimals: ±.005[.127]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE

**TRANSFORMER**

eiSos p/n: 750310564



DRAWING NO.

**750310564**

REVISIONS: SEE SHEET 1

SCALE ---

SHEET 2 OF 5